

## Side/Tail & Indicators

Lamps for side & tail illumination

**ASTRALAMP®**

| Reference No | Volt | Watt | Type | Dim(mm) |
|--------------|------|------|------|---------|
| <b>BA15s</b> |      |      |      |         |
| <b>631</b>   | 6v   | 3w   | SCC  | 18      |
| <b>205</b>   | 6v   | 5w   | SCC  | 18      |
| <b>244/8</b> | 6v   | 8w   | SCC  | 18      |
| <b>244</b>   | 6v   | 10w  | SCC  | 18      |
| <b>207</b>   | 12v  | 5w   | SCC  | 18      |
| <b>245/8</b> | 12v  | 8w   | SCC  | 18      |
| <b>245</b>   | 12v  | 10w  | SCC  | 18      |
| <b>149</b>   | 24v  | 5w   | SCC  | 18      |
| • <b>248</b> | 24v  | 5w   | SCC  | 18      |
| <b>246</b>   | 24v  | 10w  | SCC  | 18      |
| <b>874</b>   | 28v  | 7w   | SCC  | 18      |




Fig 15

### BA15s TUBULAR

|              |     |     |     |    |
|--------------|-----|-----|-----|----|
| <b>207TU</b> | 12v | 5w  | SCC | 16 |
| <b>245TU</b> | 12v | 10w | SCC | 16 |
| <b>149TU</b> | 24v | 5w  | SCC | 16 |
| <b>246TU</b> | 24v | 10w | SCC | 16 |
| <b>874TU</b> | 28v | 7w  | SCC | 16 |




Fig 16

### BA15d

|              |     |     |     |    |
|--------------|-----|-----|-----|----|
| <b>206</b>   | 6v  | 5w  | SBC | 18 |
| <b>209</b>   | 12v | 5w  | SBC | 18 |
| <b>210</b>   | 12v | 10w | SBC | 18 |
| <b>150</b>   | 24v | 5w  | SBC | 18 |
| • <b>247</b> | 24v | 5w  | SBC | 18 |
| <b>250</b>   | 24v | 10w | SBC | 18 |
| <b>875</b>   | 28v | 7w  | SBC | 18 |




Fig 17

### BA15d TUBULAR

|              |     |     |     |    |
|--------------|-----|-----|-----|----|
| <b>209TU</b> | 12v | 5w  | SBC | 16 |
| <b>210TU</b> | 12v | 10w | SBC | 16 |
| <b>150TU</b> | 24v | 5w  | SBC | 16 |
| <b>250TU</b> | 24v | 10w | SBC | 16 |
| <b>875TU</b> | 28v | 7w  | SBC | 16 |




Fig 18

### Important Notice

Lampion & Company are one of the only suppliers in the UK who produce stem type filaments and gas filled bulbs for the 24 volt 18mm range which include types 149: 150: 874: and 875, all very popular and all required to last!

The stem type filament structure (glass extended support) gives much higher resistance to vibration. Very importantly, the bulbs are gas filled as opposed to vacuum exhausted giving longer life. Combine these two improved manufacturing features together and you have a lamp that will give longer life and better service.

Our 12 volt bulbs also have stem type filaments and are gas filled from 10 watts and over.

Cheapest isn't always the best value!


## End Caps & Abbreviations

**ASTRALAMP®**

Throughout this catalogue reference is made to the dimension of each lamp either by size or abbreviation

Where an actual size is shown, eg. 8mm, this refers to the overall width of the glass envelope.

Where the dimension is shown as an abbreviation refer to the illustrations below



### Other abbreviations are:

APF - American Pre-Focus  
BC - Bayonet Cap  
BPF - British Pre-Focus  
Capless - Wedge Base  
DC - Double Contact  
ES - Edison Screw

LES - Lilliputian Edison Screw  
L & S - Long & Short Pin  
LP - Level Pin  
MCC - Miniature Centre Contact  
MES - Miniature Edison Screw  
MPF - Miniature Pre-Focus

OSP - Offset Pin  
PCB - Printed Circuit Board  
SBC - Standard Bayonet Cap  
SC - Single Contact  
SCC - Single Centre Contact