

Wiha BitFlip Sets - Insulated & Standard

“Available Fall 2008”

NEW
From Wiha

Each insulated tool individually tested to 10,000 volts and certified to 1000 Volt ac or 1500 Volt dc

Insulation according to IEC/EN 60900, ASTM F-1505-01, DIN 7437, NFPA70E

BitFlip Insulated

Blade CVM tool steel, hardened

BitFlip standard SoftFinish® handle, multi-component, cushion grip, easy access & 8 bit storage

“8 In 1 Bit Sets”

BitFlip Insulated

1000volt


380 16 Slotted/Phillips/Square BitFlip Insulated
[SHOP](#)

Wiha cushion grip handle and insulated shaft. Tested to 10,000 volts.

Set includes the following 1/4" bits:

↓ Slotted Sizes: 4.5, 6.5mm	lbs.
⊕ Phillips Sizes: 0, 1, 2, 3	.45
○ Square Sizes: 1, 2	

BitFlip Standard


380 26 Slotted/Phillips/Square BitFlip Standard
[SHOP](#)

with Wiha cushion grip handle and CVM tool steel shaft.

Set includes the following 1/4" bits:

↓ Slotted Sizes: 4.5, 6.5mm	lbs.
⊕ Phillips Sizes: 0, 1, 2, 3	.44
○ Square Sizes: 1, 2	

BitFlip Insulated

1000volt


380 17 Slotted/Phillips/TORX® BitFlip Insulated
[SHOP](#)

Wiha cushion grip handle and insulated shaft. Tested to 10,000 volts.

Set includes the following 1/4" bits:

↓ Slotted Sizes: 4.5, 6.5mm	lbs.
⊕ Phillips Sizes: 1, 2	.45
⊗ TORX® Sizes: T10, T15, T20, T25	

BitFlip Standard


380 27 Slotted/Phillips/TORX® BitFlip Standard
[SHOP](#)

with Wiha cushion grip handle and CVM tool steel shaft.

Set includes the following 1/4" bits:

↓ Slotted Sizes: 4.5, 6.5mm	lbs.
⊕ Phillips Sizes: 1, 2	.44
⊗ TORX® Sizes: T10, T15, T20, T25	

BitFlip Insulated

1000volt


380 18 Slotted/Phillips BitFlip Insulated
[SHOP](#)

Wiha cushion grip handle and insulated shaft. Tested to 10,000 volts.

Set includes the following 1/4" bits:

↓ Slotted Sizes: 4.5, 5.5, 6.5, 8.0mm	lbs.
⊕ Phillips Sizes: 0, 1, 2, 3	.45

BitFlip Standard


380 28 TORX® BitFlip Standard
[SHOP](#)

with Wiha cushion grip handle and insulated shaft.

Set includes the following 1/4" bits:

⊗ TORX® Sizes: T8, T10, T15, T20, T25, T27, T30, T40	lbs.
	.44

[PREVIOUS](#)
[NEXT](#)