

5231	9092	7310	
5231-0-00-XX-00-00-38-0 Swage mount in .094 hole. For .125 thick board.	9092-0-00-XX-00-00-38-0 Wire Termination.	7310-0-01-XX-00-00-08-0 Board edge press-fit	
SPECIFICATIONS PIN MATERIAL: Brass Alloy 360, 1/2 Hard (Except Swage pins which are annealed) DIMENSION IN INCHES TOLERANCES ON: LENGTHS: ±.005 DIAMETERS: ±.002 ANGLES: ± 2°	ORDER CODE: XXXX - X - 00 - XX - 00 - 00 - 38 - 0 BASIC PART # SPECIFY PIN FINISH: 01 200μ" TIN/LEAD OVER NICKEL 80 200μ" TIN OVER NICKEL 15 10μ" GOLD OVER NICKEL 21 20μ" GOLD OVER NICKEL 34 50μ" GOLD OVER NICKEL		