

# SPECIFICATIONS

Material: E-SEELS -- Silicone rubber polymer type ASTM D 1418

Mounting Nut: E-SEELS: ALUMINUM INSERT

Temperature Range: E-SEELS: -80°F to +400°F

Pressure Range: Exceeds 15 psi internal and 1500 psi external.



Operational Life: 50,000 actuations (minimum).

Shelf Life: Excess of 25 years.

Resistant to: Salt spray, sunlight, ozone, weather, fungus, and most acids and lubricating oils

Agency Recognition: E-SEELS and HEXSEALS are UL-listed to UL Std. 50 types 1-13, and meet CSA standards.

Installation: If a reducing adaptor is required - see page 14 of HEXSEAL catalog HEX200 for part numbers and drawing.



A	CAD COMPUTER GENERATED				9-23-
REV.	DESCRIPTION				DATE
MAXIMUM AND MINIMUM MEASUREMENTS ARE STATED DIRECTLY ON		TITLE:	BOOT-PLUNGER		ENG.
			(C1221/20)		DWN
MAT'L: SILICONE RUBBER					CARBONE
		FINISH:			CHKD.
					NICK
CLEAR			APM-HEXSEAL CORPORATION		SCALE
				4 :	DWG. NO.
				(C1221/20)	

THIS DRAWING COVERS PROPRIETARY ITEM AND IS THE PROPERTY OF THE APM-HEXSEAL CORPORATION.

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[APM HEXSEAL:](#)

[C1221/20](#)