

4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

ALL RIGHTS RESERVED.

REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	A12	REVISED PER ECO-17-001761	10MAY2017	RK	AS

TE LOGO

3

1

2

3

2A 250VAC

5A 120VAC

RATING

EPOXY SEAL

DATE CODE

04-YEAR

01-WEEK

AND

COUNTRY

OF ORIGIN

5

FUNCTION

ON ON

ALCO

8.89

[.350]

4.70±0.41

[.185±.016]

12.70

[.500]

6.86

[.270]

FUNCTION CHART

FUNCTION			
01	ON	NONE	ON
03	ON	OFF	ON
05	(ON)	OFF	(ON)
07	ON	OFF	(ON)
08	ON	NONE	(ON)
TERMINALS CONNECTED	2-3	---	1-2

NONE: NO MECHANICAL POSITION

OFF: MECHANICAL POSITION WITH NO ELECTRICAL CONNECTION

(ON): MOMENTARY ACTION

SPECIFICATIONS

RATING, B CONTACTS	.4VA MAX @20V MAX. AC OR DC
RATING, G CONTACTS-SEE NOTE 2	.4VA MAX @20V MAX. AC OR DC OR
	5A @120 VAC OR 28 VDC (RESISTIVE)
	2A @250 VAC (RESISTIVE)
RATING, Q CONTACTS	5A @120 VAC OR 28 VDC (RESISTIVE)
	2A @250 VAC (RESISTIVE)
ELECTRICAL LIFE	6,000 CYCLES AT RATED LOAD
CONTACT RESISTANCE	10 MILLIOHMS MAX INITIAL @ 2-4VDC, 100MA
INSULATION RESISTANCE	1,000 MEGOHMS MIN
DIELECTRIC WITHSTANDING VOLTAGE	1,000 V RMS AT SEA LEVEL
OPERATING TEMPRATURE	-30C TO 85C

1

ALL MATERIALS AND FINISHES SHALL COMPLY WITH EU DIRECTIVE 2002/95/EC OF 27JAN2003 (ROHS).

2

G CONTACT OPTION CAN BE USED FOR SIGNAL OR POWER LEVEL SWITCHING. IF SWITCH IS USED AT LEVELS EXCEEDING .4VA @ 20V AC/DC, SWITCH IS RENDERED FOR POWER SWITCHING ONLY DUE TO ARC REMOVAL OF GOLD PLATING. RATING MARKED ON SWITCH IS 2A 250VAC, 5A 120VAC.

3

TE CONNECTIVITY LOGO PER PER TEC-202-36.

5

DATE CODE AND COUNTRY OF ORIGIN MAY APPEAR ON EITHER SIDE OF SWITCH.

6

PANEL MOUNT BRACKET SUPPLIED WITH TERMINALS W, Z AND Z3 ONLY.

7

ACTUATOR MARKED

8

ACTUATOR MARKED

9

ACTUATOR MARKED

10

ALL LOGO, RATING, DATE CODE, AND FUNCTION MARKINGS TO BE LASER MARKED.

11

OBSOLETE

12

GRAY ACTUATOR WITH MODIFIED BRACKET (SUPPORT BRACKET TRIMMED PARALLEL TO THE PCB)

PART NUMBER SEQUENCE CHART

MODEL	FUNCTION	ACTUATOR	TERMINAL	CONTACT	ACTUATOR COLOR	BEZEL COLOR	ROHS
A1							04
	01	J1	A	B	0 BLACK (STD)	0 BLACK (STD)	
	03	J3	AV2	G	1 BROWN	1 BROWN	
	05	J50	C	Q	2 RED	2 RED	
	07	J51	V3		3 ORANGE	3 ORANGE	
	08	J52	V4		4 YELLOW	4 YELLOW	
		J2	V6		5 GREEN	5 GREEN	
		J4	V7		6 BLUE	6 BLUE	
		J60	W		8 GRAY	8 GRAY	
		J61	W4		9 WHITE	9 WHITE	
		J62	Z				
			Z3				

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:

mm [INCHES]

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC ± -

1 PLC ± -

2 PLC ± -

3 PLC ± 0.25[0.01]

4 PLC ± -

ANGLES ± 4°

FINISH -

MATERIAL -

DWN M.BINNER 06JAN05

CHK M.ZITTO 06JAN05

APVD M.ZITTO 06JAN05

PRODUCT SPEC

APPLICATION SPEC

WEIGHT

CUSTOMER DRAWING

TE Connectivity

GEMINI A SERIES ROCKER SWITCH SINGLE POLE

SIZE A2

CAGE CODE 00779

DRAWING NO C-1571986

RESTRICTED TO -







SCALE 2:1

SHEET 1 OF 5

REV A12

1471-9 (1/15)


REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
—	—	SEE SHEET 1	—	—	—




1.52[0.060]–3.17[0.125]	15.75[0.620]–15.87[0.625]
1.19[0.047]–1.50[0.059]	15.72[0.619]
PANEL THICKNESS	DIM "A"

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN	M.BINNER	06JAN05	 TE Connectivity	
		CHK	M.ZITTO	06JAN05		
		APVD	M.ZITTO	06JAN05	NAME	
		PRODUCT SPEC	—	—		
		APPLICATION SPEC	—	—	GEMINI A SERIES ROCKER SWITCH SINGLE POLE	
		—	—	—		
		WEIGHT	—	—	SIZE	CAGE CODE
		—	—	—	A2	00779
		CUSTOMER DRAWING	—	—	DRAWING NO	1571986
		—	—	—	RESTRICTED TO	—
		—	—	—	SCALE	2:1
		—	—	—	SHEET	2 OF 5
		—	—	—	REV	A12




REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
—	—	SEE SHEET 1	—	—	—



J2 SMALL




J4 LARGE




J60 SNAP-IN

J61 SNAP-IN WITH BEZEL




J62 SNAP-IN WITH BEZEL/L.E.D.

NOTE: L.E.D. NOT SUPPLIED




THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN	M.BINNER	06JAN05
DIMENSIONS: mm [INCHES]		CHK	M.ZITTO	06JAN05
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD	M.ZITTO	06JAN05
0 PLC ± -		PRODUCT SPEC		
1 PLC ± -		APPLICATION SPEC		
2 PLC ± -		WEIGHT		
3 PLC ± 0.25[0.01]		CUSTOMER DRAWING		
4 PLC ± -		SCALE		
ANGLES ± 4°		SHEET		
FINISH		REV		
-		A12		




VERTICAL SUPPORT
BRACKET

OPTION CODE	DIM "A"
V3	11.68[.460]
V4	16.00[.630]




VERTICAL SUPPORT BRACKET

OPTION CODE	DIM "A"
V6	11.68[.460]
V7	16.00[.630]



.030 THK.


PRINTED CIRCUIT



.030 THK.


OPTION	DIM A
W	18.69[.736]
W4	26.97[1.062]

W W4 WIRE WRAP



.030 THK.

Z WIRE LUG



.030 THK.

Z3 QUICK CONNECT

MATERIALS CHART

COMPONENT NAME	BASE MATERIAL	FINISH
CASE	DAP, 30-40% GF, RED, UL94 V-0, COSMIC D72/6120F	
FRAME	304 STAINLESS STEEL	
B TERMINALS & CONTACTS	C194 COPPER	GOLD OVER NICKEL
G TERMINALS & CONTACTS	C194 COPPER	GOLD OVER SILVER
Q TERMINALS & CONTACTS	C194 COPPER	SILVER
ACTUATOR	PHENOLIC, BLACK, UL94 V-1	
ROCKER CAP	NYLON, BLACK, UL94 V-1, NYTEX MG-2012N	
BUSHING & ACTUATOR LEVER	ZINC ALLOY K2	.000100-.000150 NICKEL
SPRING	MUSIC WIRE	
SUPPORT BRACKET	C2680H BRASS	TIN
PIVOT PIN	STEEL	NICKEL
TERMINAL SEAL	EPOXY, UL94 V-1, BOOM HOUSE S-9001A	

△1	A105J1AV2Q004	5-1571986-0
△1	A105J1AQ004	4-1571986-9
△1	NOT ASSIGNED	4-1571986-8
△1/△2	A103J1AV2Q004MB	4-1571986-7
	A103J61ZQ0004	4-1571986-6
	A103J51ZQ0004	4-1571986-5
△1	A103J3ZQ004	4-1571986-4
△1	A103J2ZQ004	4-1571986-3
△1	A103J2CB004	4-1571986-2
	A103J1ZQ004	4-1571986-1
△1	A103J1V3Q004	4-1571986-0
△1	A103J1AV2Q004	3-1571986-9
	A103J1AV2B004	3-1571986-8
△1	NOT ASSIGNED	3-1571986-7
	A101J61ZQ0004	3-1571986-6
	A101J51ZQ2004	3-1571986-5
	A101J51ZQ0004	3-1571986-4
△1	A101J51ZB0004	3-1571986-3
△1	NOT ASSIGNED	3-1571986-2
	A101J51Z3Q0004	3-1571986-1
	A101J51Z3G0004	3-1571986-0
	A101J51CB0004	2-1571986-9
△1	A101J50ZQ004	2-1571986-8
△1	A101J50V3Q204	2-1571986-7
△1	A101J50V3Q004	2-1571986-6
△1	A101J50AV2Q004	2-1571986-5
△1	A101J4ZQ804	2-1571986-4
	A101J4ZQ004	2-1571986-3
△1	A101J3ZQ004	2-1571986-2
△1	A101J3V3Q204	2-1571986-1
	A101J2ZQ004	2-1571986-0
	A101J2ZB904	1-1571986-9
△1	A101J2AV2Q004	1-1571986-8
	A101J1ZQ004	1-1571986-7
△1	A101J1ZB004	1-1571986-6
	A101J1V3Q004	1-1571986-5
	A101J1V3B004	1-1571986-4
△1	A101J1CQ004	1-1571986-3
	A101J1CG004	1-1571986-2
	A101J1AV2Q004	1-1571986-1
△1	A101J1AV2B004	1-1571986-0
	A101J1AQ204	1571986-9
	A101J1AQ004	1571986-8
	A101J1AB004	1571986-7
△1	NOT ASSIGNED	1571986-6
△1	NOT ASSIGNED	1571986-5
△1	NOT ASSIGNED	1571986-4
△1	NOT ASSIGNED	1571986-3
△1	NOT ASSIGNED	1571986-2
△/△1	A101J1AB004	1571986-1
	ALCO P/N	P/N

11	9	A101J1AV2Q004AM9	7-1571986-4
11	8	A101J1AV2Q004AM8	7-1571986-3
	7	A101J1AV2Q004AM	7-1571986-2
11		A108J61ZQ0004	7-1571986-0
		A108J51ZQ0004	6-1571986-9
11		A108J1ZQ004	6-1571986-8
11		A108J1V3Q004	6-1571986-7
11		A107J61ZQ0004	6-1571986-6
		A107J51ZQ0004	6-1571986-5
		A105J61ZQ0004	6-1571986-4
11		A105J61ZG0004	6-1571986-3
11		A105J52ZQ2004	6-1571986-2
		A105J51ZQ0004	6-1571986-1
		A105J4ZQ004	6-1571986-0
		A105J3ZQ004	5-1571986-9
11		A105J3CQ2004	5-1571986-8
11		A105J3CQ004	5-1571986-7
		A105J2ZQ004	5-1571986-6
11		A105J2AV2Q004	5-1571986-5
11		A105J2AQ004	5-1571986-4
		A105J1ZQ004	5-1571986-3
11		A105J1V3B004	5-1571986-2
11		A105J1CQ004	5-1571986-1
		ALCO P/N	P/N

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN <u>M.BINNER</u> 06JAN05		 TE Connectivity			
		CHK <u>M.ZITO</u> 06JAN05					
DIMENSIONS: mm [INCHES]		TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD <u>M.ZITO</u> 06JAN05		NAME	
		0 PLC ± —		GEMINI A SERIES ROCKER SWITCH SINGLE POLE			
		1 PLC ± —					
		2 PLC ± —					
		3 PLC ± 0.25[0.01]		SIZE A2			
		4 PLC ± — ± 4°					
MATERIAL —		FINISH —		APPLICATION SPEC —		CAGE CODE 00779	
		WEIGHT —		DRAWING NO G-1571986		RESTRICTED TO —	
CUSTOMER DRAWING				SCALE 2:1		SHEET 5 of 5	
				REV A12			