


I. MATERIALS AND FINISHES:
BODY - BRASS, NICKEL PLATING
CONTACT - BRASS, GOLD PLATING
C NUT, WASHER, CLAMP - BRASS, NICKEL PLATING
INSULATOR - PTFE

2. ELECTRICAL:
 - A. IMPEDANCE: 50 OHM
 - D. DIELECTRIC WITHSTANDING VOLTAGE: 500 VRMS, MIN.
3. MECHANICAL:
 - A. DURABILITY: 500 CYCLES MIN.
 - B. TEMPERATURE RANGE: -65° C TO +165° C
4. PACKAGING:
 - A. QUANTITY: SINGLE PACK
 - B. MARKING: BAG TO BE MARKED
"AMPHENOLRF, 31-3302, AND DATE CODE"

5 SHOWS CABLE ENTRY DIMENSIONS

THIS CONNECTOR IS COVERED BY U.S. PATENT 3,439,249

MIL-C-39012 INSPECTION



CUSTOMER OUTLINE DRAWING

ALL OTHER SHEETS ARE FOR INTERNAL USE ONLY

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES AND TOLERANCES ARE: 2 PLACE DECIMAL 3 PLACE DECIMAL ANGLES $\pm .015$ (0,381 mm) $\pm .005$ (0,127 mm) $\pm 1^\circ$	MATERIAL SEE NOTES	DRAWN NISCHIT MV	DATE 05-Oct-09	TITLE BNC PLUG UG-CLAMP (CATEGORY-A)	Amphenol RF Danbury, CT, USA Tainan, Taiwan Shenzhen, China www.amphenolrf.com			
					SCALE: 5.0:1 SHEET 2 OF 2			
					CAD FILE CODE ID DWG SIZE DRAWING NO. REV 74868 B 31-3302 Y			
NOTICE - These drawings, specifications, or other data (1) are, and remain the property of Amphenol Corp. (2) must be returned upon request; and (3) are confidential and not to be disclosed to any person other than those to whom they are given by Amphenol Corp. The furnishing of these drawings, specifications, or other data by Amphenol Corp., or to any other person to anyone for any purpose is not to be regarded by implication or otherwise in any manner licensing, granting rights or permitting such holder or any other person to manufacture, use or sell any product, process or design, patented or otherwise, that may in any way be related to or disclosed by said drawings, specifications, or other data.	REFERENCE MIL-C-39012/16-0102	ENGINEER D ROYCE	DATE 12-Apr-09					