

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [74323-2101](#)
Status: **Active**
Overview: MicroCross™ DVI
Description: MicroCross™ DVI Digital Single Channel, High Volume Plug Connector Sub-assembly, for PCB Mount, Gold (Au) Flash, Vertical, with key, 18 Circuits, Lead-Free

Documents:
[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)
[Product Specification PS-74320-001 \(PDF\)](#)

Agency Certification

CSA LR19980
UL E29179

General

Product Family I/O Connectors
Series [74323](#)
Application Wire-to-Board
Comments DDWG (Digital Display Working Group) Standard
Component Type I/O Plug Connector Subassembly
Overview [MicroCross™ DVI](#)
Product Name MicroCross™ DVI
Type N/A
UPC 800756566665

Physical

Boot Color N/A
Circuits (Loaded) 18
Circuits (maximum) 24
Circuits Detail Circuits 1-3,6-8,9-11,14-16,17-19,22-24 are loaded; with key
Color - Resin Black
Durability (mating cycles max) 100
Flammability 94V-0
Keying to Mating Part Yes
Lock to Mating Part Yes
Material - Metal Copper Alloy
Material - Plating Mating Gold
Material - Plating Termination Tin
Material - Resin High Temperature Thermoplastic
Net Weight 6.916/g
Number of Rows 3
Orientation Vertical
PCB Retention None
Packaging Type Tray
Panel Mount N/A
Pitch - Mating Interface 1.90mm, 2.54mm
Pitch - Termination Interface 1.90mm, 2.54mm
Plating min - Mating 0.254µm
Plating min - Termination 3.810µm
Polarized to Mating Part Yes
Polarized to PCB Yes
Ports 1
Temperature Range - Operating -20°C to +85°C
Termination Interface: Style Solder or Weld
Waterproof / Dustproof No




image - Reference only

Series

EU RoHS
ELV and RoHS
Compliant
REACH SVHC
Not Reviewed
Low-Halogen Status
Not Low-Halogen

China RoHS



Need more information on product environmental compliance?
Email productcompliance@molex.com
For a multiple part number RoHS Certificate of Compliance, [click here](#)
Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series
[74323Series](#)

Mates With
Other Receptacle components, [74320 DVI Receptacle](#), [67351 DVI Receptacle](#)

Wire Size AWG	N/A
Electrical	
Current - Maximum per Contact	3A
Grounding to Panel	Yes
Shield Type	Full Shield
Shielded	Yes
Voltage - Maximum	40V AC (RMS)
Material Info	
Reference - Drawing Numbers	
Product Specification	PS-74320-001
Sales Drawing	SD-74323-005

This document was generated on 04/04/2013

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

onlinecomponents.com