



0295



0295-0-15-XX-06-XX-10-0

Solder mount in .063 min. mounting hole
Also available on 24mm wide carrier
tape: 1,000 parts per 13" reel.
Order as: 0295-0-57-XX-06-XX-10-0


0292



0292-0-15-XX-06-XX-10-0

Solder mount in .071 min. mounting hole


0294



0294-0-15-XX-06-XX-10-0

Solder mount in .076 min. mounting hole


0398



0398-0-15-XX-06-XX-04-0

Press-fit in .066 mounting hole

0397




0397-X-15-XX-06-XX-04-0

Press-fit in .066 mounting hole

Basic Part Number	Length V
0397-0	.353
0397-1	.333
0397-2	.413


0297



0297-0-15-XX-06-XX-04-0

Press-fit in .067 mounting hole

9019/9039



90X9-X-19-XX-06-XX-10-0

Press-fit in .075 mounting hole

Basic Part Number	Head Dia. C
9019-0	.125
9039-0	.100

SPECIFICATIONS

SHELL MATERIAL:
Brass Alloy 360, 1/2 Hard

CONTACT MATERIAL:
Beryllium Copper Alloy 172, HT

DIMENSION IN INCHES
TOLERANCES ON:
LENGTHS: ±.005
DIAMETERS: ±.002
ANGLES: ± 2°

ORDER CODE: **XXXX - X - 1X - XX - 06 - XX - XX - 0**

BASIC PART #

SPECIFY SHELL FINISH:

01 200μ" TIN/LEAD OVER NICKEL

80 200μ" TIN OVER NICKEL ◇

15 10μ" GOLD OVER NICKEL ◇

SPECIFY CONTACT FINISH:

01 200μ" TIN/LEAD OVER NICKEL

80 200μ" TIN OVER NICKEL ◇

27 30μ" GOLD OVER NICKEL ◇



CONTACT

#06 CONTACT (DATA ON PAGE 220)