

IHLP® Automotive Inductors, High Temperature (155 °C) Series



FEATURES

- 6.86 mm x 6.47 mm x 3.0 mm size
- Magnetically shielded construction
- Metal alloy core
- Polarity marking available for EMI sensitive applications (see "EP" package code below for more information)
- Handles high transient current spikes without saturation
- AEC-Q200 qualified
- Material categorization: for definitions of compliance please see www.vishay.com/doc?99912



RoHS

COMPLIANT

HALOGEN
FREE
GREEN
(5-2008)

LINKS TO ADDITIONAL RESOURCES


[Product Page](#)

[3D Models](#)

[Calculators](#)

APPLICATIONS

- Automotive domain control units (DCU) and transmission / engine control
- DC/DC converters for infotainment, navigation systems, braking systems, motors, LED lighting
- Power line noise suppression and filtering

STANDARD ELECTRICAL SPECIFICATIONS


PART NUMBER	INDUCTANCE ± 20 % (μH) AT 0 A	DCR 25 °C (mΩ)		HEAT RATING CURRENT DC TYP. (A) ⁽¹⁾	SATURATION CURRENT DC TYP. (A) ⁽²⁾		SRF TYP. (MHz)
		TYP.	MAX.		20 % DROP	30 % DROP	
IHLP2525CZE_R33M5A	0.33	3.25	3.48	22.0	16.0	23.0	112
IHLP2525CZE_R47M5A	0.47	3.87	4.14	20.0	14.0	21.0	82.4
IHLP2525CZE_R68M5A	0.68	5.38	5.76	16.5	17	20	56.1
IHLP2525CZE_R82M5A	0.82	6.75	7.22	13.8	16.8	22	68.6
IHLP2525CZE_1R0M5A	1.0	7.9	8.45	12	13	15	53.2
IHLP2525CZE_1R5M5A	1.5	12.3	13.2	10.6	11.6	16	45.9
IHLP2525CZE_2R2M5A	2.2	17.1	18.3	8.1	10.8	12	31.2
IHLP2525CZE_3R3M5A	3.3	26.5	28.4	6.8	8.3	11	28.6
IHLP2525CZE_4R7M5A	4.7	35.9	38.4	5.6	5.6	6.5	25.5
IHLP2525CZE_5R6M5A	5.6	42.6	45.6	5.3	4.8	6.5	22.8
IHLP2525CZE_6R8M5A	6.8	53.8	57.6	4.4	4.4	5	19.6
IHLP2525CZE_100M5A	10	71.9	76.9	4	2.9	4	14
IHLP2525CZE_150M5A	15	98.9	105.9	3.7	2.8	4.5	10.4
IHLP2525CZE_220M5A	22	163	174	2.8	2.2	3.5	8.3

Notes


- All test data is referenced to 25 °C ambient
- Operating temperature range -55 °C to +155 °C
- The part temperature (ambient + temp. rise) should not exceed 155 °C under worst case operating conditions. Circuit design, component placement, PCB trace size and thickness, airflow and other cooling provisions all affect the part temperature. Part temperature should be verified in the end application
- Rated operating voltage (across inductor) = 75 V

⁽¹⁾ DC current (A) that will cause an approximate ΔT of 40 °C

⁽²⁾ DC current (A) that will cause L₀ to drop approximately 20 %

DIMENSIONS in inches [millimeters]

DESCRIPTION

IHLP-2525CZ-5A	22 μ H	$\pm 20\%$	EK	e3
MODEL	INDUCTANCE VALUE	INDUCTANCE TOLERANCE	PACKAGE CODE	JEDEC® LEAD (Pb)-FREE STANDARD

GLOBAL PART NUMBER

PACKAGE CODE OPTIONS


EK = tape and reel packaging (2500 pcs on 13-inch reel)
ER = tape and reel packaging (2000 pcs on 13-inch reel)
EP = tape and reel packaging (2000 pcs on 13-inch reel), includes polarity part marking

Note

- For additional packaging details see "[Packaging Methods](#)"

MAGNETIC FIELD

CONFIGURATION OF THE "B" (FLUX) FIELD FOR THE IHLP WITH POLARITY MARKING



When a positive (+) voltage is placed on the terminal marked with the polarity dot and the opposite terminal is negative (-), the resulting current flow will create a magnetic south pole on the top side of the IHLP.


For the IHLP-2525CZ-5A series, the polarity mark also indicates the "start" or "inside" lead of the winding.









Observing the polarity orientation when mounting the inductor will ensure the most consistent EMI reduction performance.







Drawing is for illustrative purposes only. The flux leakage from the inductor is minimal.


PART MARKING / POCKET TAPE ORIENTATION







For IHLP with polarity marking option



PERFORMANCE GRAPHS


PERFORMANCE GRAPHS


PERFORMANCE GRAPHS: INDUCTANCE AND Q VS. FREQUENCY


PERFORMANCE GRAPHS: INDUCTANCE AND Q VS. FREQUENCY


Disclaimer

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and / or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Hyperlinks included in this datasheet may direct users to third-party websites. These links are provided as a convenience and for informational purposes only. Inclusion of these hyperlinks does not constitute an endorsement or an approval by Vishay of any of the products, services or opinions of the corporation, organization or individual associated with the third-party website. Vishay disclaims any and all liability and bears no responsibility for the accuracy, legality or content of the third-party website or for that of subsequent links.

Vishay products are not designed for use in life-saving or life-sustaining applications or any application in which the failure of the Vishay product could result in personal injury or death unless specifically qualified in writing by Vishay. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.