






DIMENSIONS: mm (in.)



PCB Layout

**Electrical Specifications:**

- Rating: 50mA/12VDC
- Life: 50,000 cycles
- Contact Resistance: 100mΩ max.
- Insulation Resistance: 100MΩ min. @ 500VDC
- Dielectric Strength: 250VAC for 1 minute

Note:

- RoHS Compliant and are also process compatible with 260° solder

Mechanical Specifications:

- Type: SPST
- Operating Temp: -25°C to +70°C
- Operating Force: 160±50g
- Storage Temp: -30°C to +80°C
- Travel: .01+.008-.004" (.25+.02-.1mm)

Materials:

- Cover: Stainless steel
- Contacts: Silver clad stainless steel
- Terminals: Silver clad brass
- Base: Nylon, brown
- Stem: Nylon, brown

Tactile Switch (SMT)
101-0134-EV

Mountain
Switch

Available from Mouser Electronics

www.mouser.com 1-800-346-6873

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Mountain Switch:](#)

[101-0134-EV](#)