


Dual SCR POW-R-BLOK™ Modules 90 Amperes/800 Volts



Outline Drawing

Dimension	Inches	Millimeters
A	3.681 Max.	93.5 Max.
B	3.150	80
C	1.181 Max.	30 Max.
D	1.024 Max.	26 Max.
E	0.827	21
F	0.787	20
G	0.689	17.5
H	0.492	12.5
J	0.354	9
K	0.256	6.5
L	0.256 Dia.	Dia. 6.5
M	M5 Metric	M5



CM430890
Dual SCR POW-R-BLOK™ Modules
90 Amperes/800 Volts

Description:

Powerex Dual SCR POW-R-BLOK™ Modules are designed for use in applications requiring phase control and isolated packaging. The modules are isolated for easy mounting with other components on common heatsinks.

Features:

- ☐ Isolated Mounting
- ☐ Glass Passivated Chips
- ☐ Metal Baseplate
- ☐ Low Thermal Impedance

Applications:

- ☐ Battery Supplies
- ☐ Bridge Circuits
- ☐ AC and DC Motor Control
- ☐ Tap Changers
- ☐ Lighting Control

Ordering Information:

Select the complete eight digit module part number you desire from the table below.

Example: CM430890 is an 800 Volt, 90 Ampere Dual SCR POW-R-BLOK™ Module.

Type	Voltage Volts (x100)	Current Rating Amperes (90)
CM43	08	90

CM430890

Dual SCR POW-R-BLOK™ Modules

90 Amperes/800 Volts

Absolute Maximum Ratings

Characteristics	Symbol	CM430890	Units
Peak Forward Blocking Voltage	V_{DRM}	800	Volts
Transient Peak Forward Blocking Voltage (Non-Repetitive), $t < 5ms$	V_{DSM}	960	Volts
DC Forward Blocking Voltage	$V_{D(DC)}$	640	Volts
Peak Reverse Blocking Voltage	V_{RRM}	800	Volts
Transient Peak Reverse Blocking Voltage (Non-Repetitive), $t < 5ms$	V_{RSM}	960	Volts
DC Reverse Blocking Voltage	$V_{R(DC)}$	640	Volts
RMS On-State Current	$I_{T(RMS)}$	140	Amperes
Average On-State Current, $T_C = 86^\circ C$	$I_{T(AV)}$	90	Amperes
Peak One-Cycle Surge (Non-Repetitive) On-State Current (60Hz)	I_{TSM}	1800	Amperes
Peak One-Cycle Surge (Non-Repetitive) On-State Current (50Hz)	I_{TSM}	1730	Amperes
I^2t (for Fusing), 8.3 milliseconds	I^2t	15000	A ² sec
Critical Rate-of-Rise of On-State Current*	di/dt	100	Amperes/ μs
Peak Gate Power Dissipation	P_{GM}	5.0	Watts
Average Gate Power Dissipation	$P_{G(AV)}$	0.5	Watts
Peak Forward Gate Voltage	V_{GFM}	10	Volts
Peak Reverse Gate Voltage	V_{GRM}	5.0	Volts
Peak Forward Gate Current	I_{GFM}	2.0	Amperes
Storage Temperature	T_{STG}	-40 to 125	$^\circ C$
Operating Temperature	T_j	-40 to 125	$^\circ C$
Maximum Mounting Torque M6 Mounting Screw	—	26	in.-lb.
Maximum Mounting Torque M5 Terminal Screw	—	17	in.-lb.
Module Weight (Typical)	—	160	Grams
V Isolation	V_{RMS}	2000	Volts


* $T_j = 125^\circ C$, $I_G = 1.0A$, $V_D = 1/2 V_{DRM}$

Electrical and Thermal Characteristics, $T_j = 25^\circ C$ unless otherwise specified




Characteristics	Symbol	Test Conditions	CM430890	Units
Blocking State Maximums				
Forward Leakage Current, Peak	I_{DRM}	$T_j = 125^\circ C$, $V_{DRM} = \text{Rated}$	15	mA
Reverse Leakage Current, Peak	I_{RRM}	$T_j = 125^\circ C$, $V_{RRM} = \text{Rated}$	15	mA
Conducting State Maximums				
Peak On-State Voltage	V_{TM}	$I_{TM} = 270A$	1.3	Volts
Switching Minimums				
Critical Rate-of-Rise of Off-State Voltage	dv/dt	$T_j = 125^\circ C$, $V_D = 2/3 V_{DRM}$	500	Volts/ μs
Thermal Maximums				
Thermal Resistance, Junction-to-Case	$R_{\theta(J-C)}$	Per Module	0.3	$^\circ C/\text{Watt}$
Thermal Resistance, Case-to-Sink (Lubricated)	$R_{\theta(C-S)}$	Per Module	0.2	$^\circ C/\text{Watt}$
Gate Parameters Maximums				
Gate Current-to-Trigger	I_{GT}	$V_D = 6V$, $R_L = 2\Omega$	100	mA
Gate Voltage-to-Trigger	V_{GT}	$V_D = 6V$, $R_L = 2\Omega$	3.0	Volts
Non-Triggering Gate Voltage	V_{GDM}	$T_j = 125^\circ C$, $V_D = 1/2 V_{DRM}$	0.25	Volts

CM430890






Dual SCR POW-R-BLOK™ Modules
90 Amperes/800 Volts



MAXIMUM ON-STATE POWER DISSIPATION (SINUSOIDAL WAVEFORM)



MAXIMUM ALLOWABLE CASE TEMPERATURE (RECTANGULAR WAVEFORM)




CM430890


Dual SCR POW-R-BLOK™ Modules

90 Amperes/800 Volts


**MAXIMUM ON-STATE POWER DISSIPATION
(REVERSE PARALLEL CONNECTION)**




**MAXIMUM ALLOWABLE CASE TEMPERATURE
(SINGLE PHASE BRIDGE CONNECTION)**



**MAXIMUM ON-STATE POWER DISSIPATION
(SINGLE PHASE BRIDGE CONNECTION)**



**MAXIMUM ALLOWABLE CASE TEMPERATURE
(THREE PHASE BRIDGE CONNECTION)**



**MAXIMUM ON-STATE POWER DISSIPATION
(THREE PHASE BRIDGE CONNECTION)**

