



GSD



NOTES:

1. INTERFACE PER MIL-STD-348, FIG. 301-2.
2. LEAKAGE RATE SHALL NOT EXCEED 10^{-7} CC/SECOND OF TRACER GAS AT ATMOSPHERIC PRESSURE.
3. MATERIALS:
 CENTER CONTACT: BER. COPPER, ASTM-B-196
 LOCKWASHER: PHOS. BRONZE, ASTM-B-103
 GASKET: SIL. RUBBER, ZZ-R-765
 INSULATOR: TEFLON, ASTM-4894
 ALL OTHER METAL PARTS: BRASS, ASTM-B16
4. FINISHES:
 CENTER CONTACT: GOLD PLATE PER MIL-G-45204
 ALL OTHER METAL PARTS: SILVER PLATE PER QQ-S-365
5. ELECTRICAL CHARACTERISTICS:
 FREQUENCY RANGE: DC TO 11 GHz
 VOLTAGE RATING: 500 VOLTS RMS
 NOMINAL IMPEDANCE: 50 OHMS



MOUNTING HOLE

GSD

REVISIONS

ISSUE	CHANGES
10	CN 36773 E REDRAWN KH 01/17/96
11	CN 37190 C PG 11/05/96

M39012/34-0002

KAM6326

SCALE 4:1

APPROX SURFACE AREA

KA-71-04

USED ON

REF:

RCPT, BKHD,
HERMETIC SEALED, TNC

DRAWN KH DATE 01/17/96

DESIGN MJB DATE 01/18/95

APPR. DATE

KINGS
 ELECTRONICS CO., INC.
 TUCKAHOE, NEW YORK 10707

M39012/34-0002