

Duplex Multimode 62.5/125 Fiber Patch Cable (LC/SC), 10M (33-ft.)

MODEL NUMBER: **N316-10M**



Highlights

- Premium PVC 62.5/125µm multimode patch cables
- Attenuation loss meets or exceeds the latest industry standards

System Requirements

- Any fiber optic hardware or NIC card requiring multimode duplex cable with SC/LC connectors

Package Includes

- 10 meter (30-33ft) Duplex MMF Cable LC/SC 62.5/125 Fiber

Description

Tripp Lite's 10-meter (30-33ft) multimode duplex fiber optic SC/LC patch cable is manufactured from 62.5/125 zipcord fiber. The cable has LC to SC connectors, a PVC jacket and is FDDI and OFNR rated. Duplex multimode fiber is most commonly used in LAN applications.

Features

- Manufactured from 62.5/125 duplex (zipcord) fiber
- PVC jacket
- Length: 10-meter (30-33ft) Connectors: 2 SC/LC connectors on each end
- Insertion loss testing performed on every connector (0.2db typical) and provided with cable
- Beveled edge on ends of glass makes insertion of plug a breeze
- Fiber made from glass (not a polymer)
- Color coded shrouds identify transmit and receive

Specifications

General Info	
Product Group	NETWORK CABLES
OVERVIEW	
Fiber Type	62.5/125 - OM1
Intended Application	Computer Networking (Fiber)
Cable Type	MULTIMODE 62.5/125 FIBER OPTIC
Model Type	LC/SC



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

Network Speed	1Gbps
INPUT	
Cable Length (m)	10
UPC ASSIGNMENT	
Unit Carton UPC#	037332122605
PHYSICAL	
Color	Orange
Style	Fiber Optic
CONNECTIONS	
Connector A	LC
Connector B	SC
Number of Connectors	4
CERTIFICATIONS	
Certifications	ROHS
WARRANTY	
Product Warranty Period (Worldwide)	Lifetime limited warranty

© 2014 Tripp Lite. All rights reserved. All trademarks are the sole property of their respective owners. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Photos may differ slightly from final products.