

Axial Lead Diode

Schottky barrier rectifier diodes

Forward Current: 15 A

Reverse Voltage: 20 to 100 V

SB1520TL..SB15100TL

Features

- Max. solder temperature: 260 °C
- Plastic material has UL classification 94V-0
- Electrostatic discharge immunity test IEC 1000-4-2 (C=150 pF, R=150 Ohm): voltage class 20 kV

Typical Applications*

- Designed as Bypass Diodes for Solar Panels, protection application

Mechanical Data

- Plastic case: 8 x 7,5 [mm]
- Weight approx.: 2 g
- Terminals: plated terminals solderable per MIL-STD-750
- Mounting position: any
- Standard packaging: 500 pieces per ammo or 1000 pieces per reel

Footnotes

¹⁾ $I_F = -A$, $I_R = -A$, $I_{RR} = -A$

²⁾ $I_F = 5 A$, $T_j = 25 ^\circ C$

³⁾ $I_F = 15 A$, $T_j = 25 ^\circ C$

⁴⁾ Valid, if leads are kept at T_A at a distance of 0 mm from case

⁵⁾ Max. junction temperature $T_j \leq 200 ^\circ C$ in bypass mode / DC forward mode

⁶⁾ Thermal resistance from junction to lead/terminal at distance 0 mm from case




Type	Repetitive peak reverse voltage V_{RRM} V	Surge peak reverse voltage V_{RSM} V	Max. reverse recovery time $t_{rr}^{1)}$ ns	Max. forward voltage $V_F^{2)}$ V	Max. forward voltage $V_F^{3)}$ V
SB 1520TL	20	20	-	0,43	0,52
SB 1530TL	30	30	-	0,43	0,52
SB 1540TL	40	40	-	0,43	0,52
SB 1545TL	45	45	-	0,43	0,52
SB 1550TL	50	50	-	0,6	-
SB 1560TL	60	60	-	0,6	-
SB 1590TL	90	90	-	0,74	-
SB 15100TL	100	100	-	0,74	-


Absolute Maximum Ratings			
Symbol	Conditions	Values	Unit
Ta = 25 °C, unless otherwise specified			
I_{FAV}	R-load, ⁴⁾ Ta = 50 °C	15	A
I_{FRM}	f > 15 Hz, ⁴⁾	60	A
I_{FSM}	half sinus-wave	$t_p = 10 \text{ ms}$	A
	Ta = 25 °C	$t_p = 8.3 \text{ ms}$	A
i^2t	Ta = 25 °C	$t_p = 10 \text{ ms}$	A ² s
		$t_p = 8.3 \text{ ms}$	A ² s
Tj	Operating junction temperature	-50 ... +150	°C
Tj	DC forward (bypass) mode ⁵⁾	-50 ... +200	°C
Tstg	Storage temperature	-50 ... +175	°C

Characteristics					
Symbol	Conditions	min.	typ.	max.	Unit
Ta = 25 °C, unless otherwise specified					
I_R	Tj = 25 °C, VR = VRRM			500	µA
I_R	Tj = 100 °C, VR = VRRM			25	mA
Cj	at 1 MHz and applied reverse voltage of 4 V		-		pF
ERSM	L = 60 mH, Tj = 25 °C, inductive load switched off		-		mJ
Rthja	⁴⁾			-	K/W
RthjL	⁶⁾			1.8	K/W



Diode





Case: 8 x 7,5 [mm]

This is an electrostatic discharge sensitive device (ESDS), international standard IEC 60747-1, Chapter IX

* The specifications of our components may not be considered as an assurance of component characteristics. Components have to be tested for the respective application. Adjustments may be necessary. The use of SEMIKRON products in life support appliances and systems is subject to prior specification and written approval by SEMIKRON. We therefore strongly recommend prior consultation of our staff.