



LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
AJ	16		D1	ECR-12-005726	27MAR12	RK	MY



1. MATERIALS:
BODIES...BRASS PER QQ-B-626
INNER AND OUTER CONTACTS...
BERYLLIUM COPPER PER QQ-C-576
DIELECTRIC...PTFE PER ASTM D1710
FERRULE...ANNEALED COPPER PER QQ-C-576
2. FINISH:
CENTER CONTACT...GOLD PER MIL-G-45204
OTHER METAL PARTS...NICKEL PER QQ-N-290
3. FINISH:
CENTER AND OUTER CONTACT...GOLD PER MIL-G-45204
OTHER METAL PARTS...NICKEL PER QQ-N-290



RECOMMENDED STRIP LENGTHS
SCALE NTS

B	58483-1	.128	HX4-1637	4	K699	2	RG 179,187	414618-2
B	58483-1	.128	HX4-1637	4	K699	3	RG 179,187	414618-1
POSITION LETTER	TE DIE SET	HEX SIZE	DANIELS DIE SET	SELECTOR NUMBER	DANIELS POSITIONER	NOTES	CABLE	PART NUMBER
TE PRO-CRIMPER FOR BRAID CRIMP		M 22520/5-01 FOR BRAID CRIMP		M 22520/2-01 FOR CONTACT CRIMP				
TOOLING INFORMATION								

THIS DRAWING IS A CONTROLLED DOCUMENT.			DWN B. WERNER 13/JUL/93		 TE Connectivity			
DIMENSIONS: mm [INCHES]			CHK J. MCLEOD 13/JUL/93					
			APVD J. MCLEOD 13/JUL/93		NAME 75 OHM SMB PLUG			
			PRODUCT SPEC —					
			APPLICATION SPEC —					
			WEIGHT —					
MATERIAL			FINISH		SIZE A2	CAGE CODE 00779	DRAWING NO C=414618	RESTRICTED TO —
SEE NOTES			SEE NOTES		CUSTOMER DRAWING			
					SCALE 5:1	SHEET 1 of 1	REV D1	