



NOTES

1. APPLICABLE CRIMPING CONTACT : JRC-PC-212 (AWG#24 TO 20)  
JRC-PC-222 (AWG#28 TO 24)
2. APPLICABLE CRIMP CONTACT EXTRACTION TOOL : JRC-TP(CL150-0035-0)
3. THE RECOMMENDED CLAMP TORQUE OF REF. NO. ⑤ TO BE 4 TO 4.5N·m.
4. ACROSS FLATS OF HEXAGON HEAD OF REF. NO. ⑧ TO BE 1.27mm.  
THE RECOMMENDED CLAMP TORQUE OF REF. NO. ⑧ TO BE 0.3 TO 0.4N·m.  
LOCTITE 242, HENKEL JAPAN IS RECOMMENDED TO PREVENT  
REF. NO. ⑧ FROM LOOSENING.
5. ROTATION EXAMPLES OF REF. NO. ① AND ⑤ ARE SHOWN.
6. THE CABLE PULL AND TWISTING AND OTHER CHARACTERISTICS  
MAY DIFFER, DEPENDING ON THE CABLE STRUCTURE.  
PLEASE CONFIRM BEFORE THE USE.

4	ALUMINUM ALLOY	MATTE FINISH NICKEL PLATED	8	STEEL	NICKEL PLATING.	HEX SOCKET SET SCREW M2.6X0.45X2
3	PHOSPHOR BRONZE	NICKEL PLATING	7	BRASS	NICKEL PLATING	M3X0.5X10
2	POLYCARBONATE	(BLACK) UL94V-0	6	ALUMINUM ALLOY	MATTE FINISH NICKEL PLATED	
1	ALUMINUM ALLOY	MATTE FINISH NICKEL PLATED	5	ALUMINUM ALLOY	MATTE FINISH NICKEL PLATED	
NO.	MATERIAL	FINISH . REMARKS	NO.	MATERIAL	FINISH . REMARKS	
UNITS mm	Ø	SCALE 1 : 1	COUNT	DESCRIPTION OF REVISIONS	DESIGNED	CHECKED

 <b>HIROSE</b> <b>ELECTRIC</b> <b>CO., LTD.</b>	APPROVED : SU. OBARA	11.11.28	DRAWING NO.	EDC4-029003-71
	CHECKED : HY. KISHI	11.11.28	PART NO.	JR21PK-10PCC71
	DESIGNED : DS. MATSUNE	11.11.28	CODE NO.	CL114-0570-0-71
	DRAWN : TR. SATO	11.11.26		△ 1/1