

TL-161 Holding Catch



Characteristic

Simple catch made of resin.


Application

Measuring instruments /
Machine tools / Furniture


Model No.	Pullout Strength N(kgf)	Net Weight(g)	Code No.
TL-161	approx.29.4 (3)	1.9	1274

Parts List

No.	Part Name	Material	Finish	Quantity
1	Keeper	PP	Brown	1
2	Catch	POM		1



TL-55 Roller Catch




Characteristic

A smooth push-in/ pullout operation by its roller mechanism.

Application

Measuring instruments /
Machine tools / Furniture



Parts List

No.	Part Name	TL-55-1, 2		TL-55-3, 4		Quantity
		Material	Finish	Material	Finish	
1	Housing	SPCC	Uc	SUS430		1
2	Spring	SWRM	—	SUS304		1
3	Shaft (A)	SWCH				1
4	Arm	SPCC	Uc	SUS430		2
5	Shaft (B)	SWCH				2
6	Roller	PE	White	PP	White	2
7	Keeper	SPCC	Uc	SUS304	—	1

Model No.	a	b	c	d	Pullout Strength N(kgf)	Net Weight(g)	Code No.
TL-55-1	24	19.5	26.0	7.5	approx.24.5 (2.5)	16.3	1066
TL-55-2	20	17.0	20.5	7.0	approx.14.7 (1.5)	9.4	1067
TL-55-3	24	19.5	26.0	8.0	approx.29.4 (3.0)	14.5	1103
TL-55-4	20	17.0	20.5	6.5	approx.19.6 (2.0)	9.2	1104

Size List (Reference)

Model No.	A	B	C	D	E	F	G	H	I	J	K	L	M	N	O	P
TL-55-1	32	24	3.5	7.8	3.5	14.7	2.8	15.5	t 0.8	(7.5)	27.5	19.5	φ 3.6	9.5	16	t 0.8
TL-55-2	28	20	3.0	7.4	2.5	12.5		13.5	t 0.6	(7)	22.5	17.0	φ 2.8	7.0	12	t 0.6
TL-55-3	32	24	3.5	7.8	3.2	15	2.5	15.5	t 0.8	(7.5)	27.5	19.5	φ 3.6	9.5	16	t 0.8
TL-55-4	28	20	3.0	7.4	2.5	12.5		13.5	t 0.6	(6.5)	22.5	17.0	φ 2.8	7.0	12	t 0.6