


# 54ACT16241, 74ACT16241 16-BIT BUFFERS/DRIVERS WITH 3-STATE OUTPUTS

SCAS189A – MARCH 1990 – REVISED APRIL 1996

- Members of the Texas Instruments *Widebus*™ Family
- Inputs Are TTL-Voltage Compatible
- 3-State Outputs Drive Bus Lines or Buffer Memory Address Registers
- Flow-Through Architecture Optimizes PCB Layout
- Distributed  $V_{CC}$  and GND Pin Configuration Minimizes High-Speed Switching Noise
- *EPIC*™ (Enhanced-Performance Implanted CMOS) 1- $\mu$ m Process
- 500-mA Typical Latch-Up Immunity at 125°C
- Package Options Include Plastic 300-mil Shrink Small-Outline (DL) Packages Using 25-mil Center-to-Center Pin Spacings and 380-mil Fine-Pitch Ceramic Flat (WD) Packages Using 25-mil Center-to-Center Pin Spacings

54ACT16241 . . . WD PACKAGE  
74ACT16241 . . . DL PACKAGE  
(TOP VIEW)



## description

The 'ACT16241 are 16-bit buffers or line drivers designed specifically to improve both the performance and density of 3-state memory address drivers, clock drivers, and bus-oriented receivers and transmitters. The devices can be used as four 4-bit buffers, two 8-bit buffers, or one 16-bit buffer. These devices provide true outputs and complementary output-enable (OE and  $\overline{OE}$ ) inputs.

The 74ACT16241 is packaged in TI's shrink small-outline package, which provides twice the I/O pin count and functionality of standard small-outline packages in the same printed-circuit-board area.

The 54ACT16241 is characterized for operation over the full military temperature range of –55°C to 125°C. The 74ACT16241 is characterized for operation from –40°C to 85°C.



Please be aware that an important notice concerning availability, standard warranty, and use in critical applications of Texas Instruments semiconductor products and disclaimers thereto appears at the end of this data sheet.

EPIC and Widebus are trademarks of Texas Instruments Incorporated.

UNLESS OTHERWISE NOTED this document contains PRODUCTION DATA information current as of publication date. Products conform to specifications per the terms of Texas Instruments standard warranty. Production processing does not necessarily include testing of all parameters.

**TEXAS  
INSTRUMENTS**

POST OFFICE BOX 655303 • DALLAS, TEXAS 75265


Copyright © 1996, Texas Instruments Incorporated

FUNCTION TABLES

| INPUTS |   | OUTPUT<br>Y |
|--------|---|-------------|
| OE     | A |             |
| L      | H | H           |
| L      | L | L           |
| H      | X | Z           |


| INPUTS |   | OUTPUT<br>Y |
|--------|---|-------------|
| OE     | A |             |
| H      | H | H           |
| H      | L | L           |
| L      | X | Z           |

logic symbol†



† This symbol is in accordance with ANSI/IEEE Std 91-1984 and IEC Publication 617-12.

**logic diagram (positive logic)**



**absolute maximum ratings over operating free-air temperature range (unless otherwise noted)<sup>†</sup>**

|                                                                                                       |                            |
|-------------------------------------------------------------------------------------------------------|----------------------------|
| Supply voltage range, $V_{CC}$                                                                        | –0.5 V to 7 V              |
| Input voltage range, $V_I$ (see Note 1)                                                               | –0.5 V to $V_{CC} + 0.5$ V |
| Output voltage range, $V_O$ (see Note 1)                                                              | –0.5 V to $V_{CC} + 0.5$ V |
| Input clamp current, $I_{IK}$ ( $V_I < 0$ or $V_I > V_{CC}$ )                                         | ±20 mA                     |
| Output clamp current, $I_{OK}$ ( $V_O < 0$ or $V_O > V_{CC}$ )                                        | ±50 mA                     |
| Continuous output current, $I_O$ ( $V_O = 0$ to $V_{CC}$ )                                            | ±50 mA                     |
| Continuous current through $V_{CC}$ or GND                                                            | ±400 mA                    |
| Maximum package power dissipation at $T_A = 55^\circ\text{C}$ (in still air) (see Note 2): DL package | 1.2 W                      |
| Storage temperature range, $T_{Stg}$                                                                  | –65°C to 150°C             |

<sup>†</sup> Stresses beyond those listed under "absolute maximum ratings" may cause permanent damage to the device. These are stress ratings only, and functional operation of the device at these or any other conditions beyond those indicated under "recommended operating conditions" is not implied. Exposure to absolute-maximum-rated conditions for extended periods may affect device reliability.

- NOTES:
1. The input and output voltage ratings may be exceeded if the input and output current ratings are observed.
  2. The maximum package power dissipation is calculated using a junction temperature of 150°C and a board trace length of 750 mils.

# 54ACT16241, 74ACT16241

## 16-BIT BUFFERS/DRIVERS

### WITH 3-STATE OUTPUTS

SCAS189A – MARCH 1990 – REVISED APRIL 1996

#### recommended operating conditions (see Note 3)

|                     |                                    | 54ACT16241 |     |          | 74ACT16241 |     |          | UNIT |
|---------------------|------------------------------------|------------|-----|----------|------------|-----|----------|------|
|                     |                                    | MIN        | NOM | MAX      | MIN        | NOM | MAX      |      |
| $V_{CC}$            | Supply voltage                     | 4.5        | 5   | 5.5      | 4.5        | 5   | 5.5      | V    |
| $V_{IH}$            | High-level input voltage           | 2          |     |          | 2          |     |          | V    |
| $V_{IL}$            | Low-level input voltage            |            |     | 0.8      |            |     | 0.8      | V    |
| $V_I$               | Input voltage                      | 0          |     | $V_{CC}$ | 0          |     | $V_{CC}$ | V    |
| $V_O$               | Output voltage                     | 0          |     | $V_{CC}$ | 0          |     | $V_{CC}$ | V    |
| $I_{OH}$            | High-level output current          |            |     | –24      |            |     | –24      | mA   |
| $I_{OL}$            | Low-level output current           |            |     | 24       |            |     | 24       | mA   |
| $\Delta t/\Delta v$ | Input transition rise or fall rate | 0          |     | 10       | 0          |     | 10       | ns/V |
| $T_A$               | Operating free-air temperature     | –55        |     | 125      | –40        |     | 85       | °C   |

NOTE 3: Unused inputs must be held high or low to prevent them from floating.

#### electrical characteristics over recommended operating free-air temperature range (unless otherwise noted)

| PARAMETER                | TEST CONDITIONS                                        | $V_{CC}$ | $T_A = 25^\circ\text{C}$ |     |           | 54ACT16241 |         | 74ACT16241 |         | UNIT          |
|--------------------------|--------------------------------------------------------|----------|--------------------------|-----|-----------|------------|---------|------------|---------|---------------|
|                          |                                                        |          | MIN                      | TYP | MAX       | MIN        | MAX     | MIN        | MAX     |               |
| $V_{OH}$                 | $I_{OH} = -50\ \mu\text{A}$                            | 4.5 V    | 4.4                      |     |           | 4.4        |         | 4.4        |         | V             |
|                          |                                                        | 5.5 V    | 5.4                      |     |           | 5.4        |         | 5.4        |         |               |
|                          | $I_{OH} = -24\ \text{mA}$                              | 4.5 V    | 3.94                     |     |           | 3.8        |         | 3.8        |         |               |
|                          |                                                        | 5.5 V    | 4.94                     |     |           | 4.8        |         | 4.8        |         |               |
|                          | $I_{OH} = -75\ \text{mA}^\dagger$                      | 5.5 V    |                          |     |           | 3.85       |         | 3.85       |         |               |
| $V_{OL}$                 | $I_{OL} = 50\ \mu\text{A}$                             | 4.5 V    |                          |     | 0.1       |            | 0.1     |            | 0.1     | V             |
|                          |                                                        | 5.5 V    |                          |     | 0.1       |            | 0.1     |            | 0.1     |               |
|                          | $I_{OL} = 24\ \text{mA}$                               | 4.5 V    |                          |     | 0.36      |            | 0.44    |            | 0.44    |               |
|                          |                                                        | 5.5 V    |                          |     | 0.36      |            | 0.44    |            | 0.44    |               |
|                          | $I_{OL} = 75\ \text{mA}^\dagger$                       | 5.5 V    |                          |     |           | 1.65       |         | 1.65       |         |               |
| $I_I$                    | $V_I = V_{CC}$ or GND                                  | 5.5 V    |                          |     | $\pm 0.1$ |            | $\pm 1$ |            | $\pm 1$ | $\mu\text{A}$ |
| $I_{OZ}$                 | $V_O = V_{CC}$ or GND                                  | 5.5 V    |                          |     | $\pm 0.5$ |            | $\pm 5$ |            | $\pm 5$ | $\mu\text{A}$ |
| $I_{CC}$                 | $V_I = V_{CC}$ or GND, $I_O = 0$                       | 5.5 V    |                          |     | 8         |            | 80      |            | 80      | $\mu\text{A}$ |
| $\Delta I_{CC}^\ddagger$ | One input at 3.4 V,<br>Other inputs at $V_{CC}$ or GND | 5.5 V    |                          |     | 0.9       |            | 1       |            | 1       | mA            |
| $C_i$                    | $V_I = V_{CC}$ or GND                                  | 5 V      |                          | 4.5 |           |            |         |            |         | pF            |
| $C_o$                    | $V_O = V_{CC}$ or GND                                  | 5 V      |                          | 13  |           |            |         |            |         | pF            |

<sup>†</sup> Not more than one output should be tested at a time, and the duration of the test should not exceed 10 ms.

<sup>‡</sup> This is the increase in supply current for each input that is at one of the specified TTL voltage levels rather than 0 V or  $V_{CC}$ .


switching characteristics over recommended operating free-air temperature range,  
 $V_{CC} = 5\text{ V} \pm 0.5\text{ V}$  (unless otherwise noted) (see Figure 1)

| PARAMETER | FROM<br>(INPUT)              | TO<br>(OUTPUT) | $T_A = 25^\circ\text{C}$ |     |      | 54ACT16241 |      | 74ACT16241 |      | UNIT |
|-----------|------------------------------|----------------|--------------------------|-----|------|------------|------|------------|------|------|
|           |                              |                | MIN                      | TYP | MAX  | MIN        | MAX  | MIN        | MAX  |      |
| $t_{PLH}$ | A                            | Y              | 3.3                      | 6.5 | 8.4  | 3.3        | 9.5  | 3.3        | 9.5  | ns   |
| $t_{PHL}$ |                              |                | 2.3                      | 6.3 | 8.2  | 2.3        | 9.1  | 2.3        | 9.1  |      |
| $t_{PZH}$ | $\overline{\text{OE}}$ or OE | Y              | 2.3                      | 6.5 | 8.3  | 2.3        | 9.4  | 2.3        | 9.4  | ns   |
| $t_{PZL}$ |                              |                | 2.9                      | 7.3 | 9.3  | 2.9        | 10.5 | 2.9        | 10.5 |      |
| $t_{PHZ}$ | $\overline{\text{OE}}$ or OE | Y              | 4.3                      | 8.9 | 10.6 | 4.3        | 11.6 | 4.3        | 11.6 | ns   |
| $t_{PLZ}$ |                              |                | 4                        | 8.1 | 9.8  | 4          | 10.7 | 4          | 10.7 |      |

operating characteristics,  $V_{CC} = 5\text{ V}$ ,  $T_A = 25^\circ\text{C}$


| PARAMETER |                               | TEST CONDITIONS  |                                           | TYP | UNIT |
|-----------|-------------------------------|------------------|-------------------------------------------|-----|------|
| $C_{pd}$  | Power dissipation capacitance | Outputs enabled  | $C_L = 50\text{ pF}$ , $f = 1\text{ MHz}$ | 43  | pF   |
|           |                               | Outputs disabled |                                           | 10  |      |

## PARAMETER MEASUREMENT INFORMATION




LOAD CIRCUIT

| TEST              | S1                |
|-------------------|-------------------|
| $t_{PLH}/t_{PHL}$ | Open              |
| $t_{PLZ}/t_{PZL}$ | 2 $\times V_{CC}$ |
| $t_{PHZ}/t_{PZH}$ | GND               |



VOLTAGE WAVEFORMS



VOLTAGE WAVEFORMS

- NOTES:
- $C_L$  includes probe and jig capacitance.
  - Waveform 1 is for an output with internal conditions such that the output is low except when disabled by the output control. Waveform 2 is for an output with internal conditions such that the output is high except when disabled by the output control.
  - All input pulses are supplied by generators having the following characteristics:  $PRR \leq 1\text{ MHz}$ ,  $Z_O = 50\text{ }\Omega$ ,  $t_r = 3\text{ ns}$ ,  $t_f = 3\text{ ns}$ .
  - The outputs are measured one at a time with one input transition per measurement.

Figure 1. Load Circuit and Voltage Waveforms

## **IMPORTANT NOTICE**

Texas Instruments and its subsidiaries (TI) reserve the right to make changes to their products or to discontinue any product or service without notice, and advise customers to obtain the latest version of relevant information to verify, before placing orders, that information being relied on is current and complete. All products are sold subject to the terms and conditions of sale supplied at the time of order acknowledgement, including those pertaining to warranty, patent infringement, and limitation of liability.

TI warrants performance of its semiconductor products to the specifications applicable at the time of sale in accordance with TI's standard warranty. Testing and other quality control techniques are utilized to the extent TI deems necessary to support this warranty. Specific testing of all parameters of each device is not necessarily performed, except those mandated by government requirements.

CERTAIN APPLICATIONS USING SEMICONDUCTOR PRODUCTS MAY INVOLVE POTENTIAL RISKS OF DEATH, PERSONAL INJURY, OR SEVERE PROPERTY OR ENVIRONMENTAL DAMAGE ("CRITICAL APPLICATIONS"). TI SEMICONDUCTOR PRODUCTS ARE NOT DESIGNED, AUTHORIZED, OR WARRANTED TO BE SUITABLE FOR USE IN LIFE-SUPPORT DEVICES OR SYSTEMS OR OTHER CRITICAL APPLICATIONS. INCLUSION OF TI PRODUCTS IN SUCH APPLICATIONS IS UNDERSTOOD TO BE FULLY AT THE CUSTOMER'S RISK.

In order to minimize risks associated with the customer's applications, adequate design and operating safeguards must be provided by the customer to minimize inherent or procedural hazards.

TI assumes no liability for applications assistance or customer product design. TI does not warrant or represent that any license, either express or implied, is granted under any patent right, copyright, mask work right, or other intellectual property right of TI covering or relating to any combination, machine, or process in which such semiconductor products or services might be or are used. TI's publication of information regarding any third party's products or services does not constitute TI's approval, warranty or endorsement thereof.