

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [31372-1100](#)
Status: **Active**
Overview: [Stac64™ Single, Multi-Pocket and Hybrid Header System](#)
Description: [Stac64™ Hybrid Receptacle Assembly, 10 Circuit, Gray, Polarization B](#)



Series

image - Reference only

Documents:
[3D Model](#)
[Drawing \(PDF\)](#)
[Product Specification PS-31372-100 \(PDF\)](#)
[Application Specification AS-31372-100 \(PDF\)](#)
[Application Specification AS-34729-020 \(PDF\)](#)
[RoHS Certificate of Compliance \(PDF\)](#)

General	
Product Family	Crimp Housings
Series	31372
Application	Power, Wire-to-Board
Comments	Polarization B, 6 x 1.50 and 4 x 2.8
Overview	Stac64™ Single, Multi-Pocket and Hybrid Header System
Product Name	Stac64™
UPC	883906883416

Physical	
Circuits (maximum)	10
Circuits Detail	10
Color - Resin	Gray
Gender	Female
Glow-Wire Compliant	No
Keying to Mating Part	None
Lock to Mating Part	Yes
Material - Resin	Modified Polystyrene
Net Weight	8.060/g
Number of Rows	2
Packaging Type	Carton
Panel Mount	No
Pitch - Mating Interface	3.50mm, 5.25mm
Polarized to Mating Part	Yes
Ports	10
Stackable	No
Temperature Range - Operating	-40°C to +100°C

Electrical	
Current - Maximum per Contact	22A, 30A

Material Info

Reference - Drawing Numbers	
Application Specification	AS-31372-100, AS-34729-020
Product Specification	PS-31372-100
Sales Drawing	SD-31372-900

EU RoHS
ELV and RoHS
Compliant
REACH SVHC
Contains SVHC: No
Low-Halogen Status
Low-Halogen

China RoHS



Need more information on product environmental compliance?

Email productcompliance@molex.com
For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series
[31372Series](#)

Mates With
[34696 Stac64 Right Angle Assembly](#). [34695 Stac64 Vertical Assembly](#)

Use With
[MX150™ Terminal](#) [33012](#)

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[31372-1100](#)