


## Duplex Multimode 62.5/125 Fiber Patch Cable (SC/SC), 100M (328-ft.)

MODEL NUMBER: **N306-100M**



### Highlights

- Premium PVC 62.5/125µm multimode patch cables
- Attenuation loss meets or exceeds the latest industry standards

### System Requirements

- Any fiber optic hardware or NIC card requiring multimode duplex cable with SC/SC connectors

### Package Includes

- 328 -ft. (100 meter) duplex MMF cable SC/SC 62.5/125 fiber

### Description

Tripp Lite's 328-ft. ( 100 meters ) multimode duplex fiber optic SC/SC patch cable is manufactured from 62.5/125 zipcord fiber. The cable has SC connectors on each end, a PVC jacket and is FDDI and OFNR rated. Duplex multimode fiber is most commonly used in LAN applications.

### Features

- Manufactured from 62.5/125 duplex (zipcord) fiber
- PVC jacket
- Length: 328-ft. ( 100 meters ) Connectors: 2 SC connectors on each end
- Insertion loss testing performed on every connector (0.2db typical) and provided with cable
- Beveled edge on ends of glass makes insertion of plug a breeze
- Fiber made from glass (not a polymer)
- Color coded shrouds identify transmit and receive
- Fiber optic distributed data interface (FDDI) rated
- OFNR (riser rated)

## Specifications

General Info	
Product Group	NETWORK CABLES
OVERVIEW	
Fiber Type	62.5/125 - OM1
Intended Application	Computer Networking (Fiber)



**Tripp Lite**  
1111 W. 35th Street  
Chicago, IL 60609 USA  
Telephone: 773.869.1234  
[www.tripplite.com](http://www.tripplite.com)

Cable Type	MULTIMODE 62.5/125 FIBER OPTIC
Model Type	SC/SC
Network Speed	1Gbps
<b>INPUT</b>	
Cable Length (ft.)	328
Cable Length (m)	100
<b>UPC ASSIGNMENT</b>	
Unit Carton UPC#	037332157218
<b>PHYSICAL</b>	
Color	Orange
Style	Fiber Optic
<b>CONNECTIONS</b>	
Connector A	SC
Connector B	SC
Number of Connectors	4
<b>WARRANTY</b>	
Product Warranty Period (Worldwide)	Lifetime limited warranty

© 2014 Tripp Lite. All rights reserved. All trademarks are the sole property of their respective owners. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Photos may differ slightly from final products.