

SIZE A3	CAGE CODE 00779	DRAWING NO C- 5-1440002-4	RESTRICTED TO —
		SCALE 3:1	SHEET 1 OF 2
			REV B1

4

THIS DRAWING IS UNPUBLISHED.

© COPYRIGHT

3

RELEASED FOR PUBLICATION

ALL RIGHTS RESERVED.

2

LOC
HB

DIST

1

REVISIONS

??

P	LTR	DESCRIPTION	ECN	DATE	DWN	APVD

DRILLING DIAGRAM (BOTTOM VIEW)

27.6 ± 0.1

12 ± 0.05

22 ± 0.1

5.8 ± 0.05

6.2 ± 0.05

2-φ1.6 ± 0.1 (HOLE)

3'

4'

3

CONNECTION DIAGRAM

(BOTTOM VIEW)

(TOP VIEW)

(BOTTOM VIEW)

1

2

3

3'

4

4'

5-1440002-9	PCF-148D2M,000	48V	PCF-148D2M	f
5-1440002-8	PCF-124D2M,000	24V	PCF-124D2M	e
3-1419153-4	PCF-112D2M,000	12V	PCF-112D2M	d
5-1440002-6	PCF-109D2M,000	9V	PCF-109D2M	c
5-1440002-5	PCF-106D2M,000	6V	PCF-106D2M	b
5-1440002-4	PCF-105D2M,000	5V	PCF-105D2M	a
PART NO	DESCRIPTION	PART B	PART A	ITEM

RELAY TYPE

		EPOXY RESIN	SEAL	17
		POLYURETHANE Cu WIRE	MAGNETIC WIRE	16
UL 94V-0		PPS	CARD	15
UL 94V-0		PBT	CASE	14
UL 94V-0		PBT	BASE	13
UL 94V-0		PBT	BOBBIN	12
	SOLDER DIP	Cu ALLOY	COIL TERMINAL R	11
	SOLDER DIP	Cu ALLOY	COIL TERMINAL L	10
		STAINLESS	HINGE SPRING	9
		Ag ALLOY	STATIONARY CONTACT	8
		Ag ALLOY	MOVABLE CONTACT	7
	SOLDER DIP	Cu ALLOY	MOVABLE SPRING	6
	SOLDER DIP	Cu ALLOY	STATIONARY TERMINAL	5
	SOLDER DIP	Cu ALLOY	MOVABLE TERMINAL	4
	Ni PLATED	STEEL	CORE	3
	Ni PLATED	STEEL	ARMATURE	2
	Ni PLATED	STEEL	YOKE	1
INCOMBUSTIBILITY	TREATMENT	MATERIAL	DESCRIPTION	ITEM

DIMENSIONS:
mm

MATERIAL
SEE MATERIAL TABLE

FINISH
—

TOLERANCES UNLESS
OTHERWISE SPECIFIED:

0 PLC ±
1 PLC ±
2 PLC ±
3 PLC ±
4 PLC ±
ANGLES ±

—

DWN
CHK
APVD
PRODUCT SPEC
APPLICATION SPEC
WEIGHT
CUSTOMER DRAWING

NAME
PCF-D2M CUSTOMER DRAWING

SIZE
A3

CAGE CODE
00779

DRAWING NO
C= 5-1440002-4

RESTRICTED TO
—

SCALE
3:1

SHEET
2 OF 2

REV
B1