




ELECTRICAL CHARACTERISTICS

- Impedance: 50 Ohm
- Working frequency: 1GHz max
- Dielectric with standing voltage: 600V
- Insulation resistance 5000: 14 Ohm
- Contact resistance < 5 mOhm
- Insertion loss: < 0.2 dB

MECHANICAL CHARACTERISTICS

- Mating force per set of contact 0.4 N to 9 N
- Mating endurance 500
- Temperature -55°C to +125 °C

TOOLING

- Coaxial contact extraction tool 8630-07A

DM537435001NCLF	RIGHT ANGLE SOCKET COAXIAL CONTACT	1.70	2.46	3.13	3.84	RG 188 A/U RG 179 B/U RG 316 /U
PART NUMBER	DESIGNATION	$\phi A^{+0.10}_0$	$\phi B^{\pm 0.05}$	$\phi C^{+0.10}_0$	$\phi D^{\pm 0.10}$	CABLE REF.

NOTE:RoHS INFORMATIONS

- The "LF" product meets European union Directives and other country regulations as described in GS-22-008.
- The product is not intended to be exposed to a manufacturing solder process.
- Packaging spec: see GS-14-920.

rev	ecn no	dr	date
A	LS05-0086	MPE	2005/10/12
B	LS05-0107	MPE	2005/12/20
C	LS07-0001	MPE	2007/01/09
D	F10-0086	LSA	2010/08/20
-	-	-	-
-	-	-	-
-	-	-	-

www.fciconnect.com			surface ISO 1302	tolerance std ISO 406 ISO 1101	projection size	mm Scale
			TOLERANCES UNLESS OTHERWISE SPECIFIED			5
Dr	PESSON	2005/10/12	ANGULAR	LINEAR	0.X	± 0.1
Eng	LEGARE	2005/10/12			0.XX	± 0.1
Chr	LEGARE	2005/10/12	0.XX ± 2		0.XXX	± 0.1
Appr	LEGARE	2005/10/12	Product family			ECN F10-0086
			D-SUB			Spec ref -
FCI			RIGHT ANGLE SOCKET COAXIAL CONTACT			Rev. D
			SOLDER TO CABLE			
catalog no			C01-8639-2150			
			CUSTOMER			sheet 1 of 1

European Views