




The S series was developed for the high voltage ATE market, where printed circuit board (PCB) space is at a premium, the S series high voltage reed relay offers a 3 or 5* kV isolation performance in a 30mm size package. With low contact resistance, the S series is suitable for many high voltage applications at DC and low frequency, where performance and reliability are paramount.



- **Compact Footprint**
- **Designed Specifically for High Voltage**
- **Rhodium Contacts for Low Resistance**
- **3 or 5kV * Isolation Between Contacts**
- **Excellent Lifetime Characteristics**

Mechanical Dimensions


All dimensions are in Millimetres (inches)



PIN SIZE

PINS 1, 2, 5 & 6 0.7 Square (0.025")
PINS 3 & 4 0.8 (0.031") dia.

CIRCUIT DIAGRAM



(Viewed from Underside)

USA

Cynergy3 Components
2320 Paseo de las Americas, Suite 104
San Diego, CA 92154
Sales & Tech Support (866) 258-5057
Email: sales@cynergy3.com

EUROPE - UK

Cynergy3 Components Ltd. +44 (0) 1202 897969
7 Cobham Road Fax +44 (0) 1202 891918
Ferndown Industrial Estate Email: sales@cynergy3.com
Wimborne, Dorset BH21 7PE

Contact	Units	Conditions	3kV Form A			5kV Form A		
Contact Materials			Rhodium			Rhodium		
Isolation Across Contacts	kV	DC or AC peak	3			5*		
Max. Switching Power	W		10			10		
Max. Switching Voltage	V	DC or AC peak	20			20		
Max. Switching Current	A	DC or AC peak	0.5			0.5		
Max. Carry Current	A	DC or AC rms (60Hz)	1.5			1.5		
Capacitance Across Contacts	pF	Coil/Screen Grounded	<0.1			<0.1		
Lifetime	Operations	Dry Switching	10 ⁹			10 ⁹		
Lifetime	Operations	10W Switching	10 ⁸			10 ⁸		
Contact Resistance	mOhms	Maximum (Typical)	80 (30)			80 (30)		
Insulation Resistance Contact to All Other Terminals	Ohms	Minimum (Typical)	10 ¹⁰ (10 ¹³)			10 ¹⁰ (10 ¹³)		
Coil at 20°C			5V	12V	24V	5V	12V	24V
Must Operate	V	DC	3.7	9	20	3.7	9	20
Must Release	V	DC	0.5	1.25	3	0.5	1.25	3
Operate Time	ms	Diode Fitted	1.0	1.0	1.0	1.0	1.0	1.0
Release Time	ms	Diode Fitted	0.5	0.5	0.5	0.5	0.5	0.5
Resistance	Ohms		140	600	1000	140	600	1000
Construction								
Isolation Contact to Coil to All Other Terminals	kV Ohms	DC or AC peak Minimum (Typical)	5			5		
Environmental								
Operating Temperature Range	°C		-20 to +70			-20 to +70		

Part Numbering System

Reedswitch Size - **S** _____ **S** **A** **R** **9** **12** **05**
 Contact Form - **A**: Form A _____
 Contact Material - **R**: Rhodium _____
 Moulding Reference Number _____
 Coil Voltage - **05**: 5V, **12**: 12V, **24**: 24V _____
 Isolation Between Contacts - **03**: 3kV, **05**: 5kV _____

* DC only, Pin 3 +HV