


MATED WITH: PASSEND ZU: —	LOC AI	DIST —	REVISIONS						
			P	LTR	AENDERUNGEN DESCRIPTION BESCHREIBUNG		DATE	DWN	APVD
PROJEKT NR.: —			B2	REVISED PER ECO-11-005150			21MAR11	RK	HMR
Customer Drawing for PN 964294 SEE 1355364									
RELEASED FOR PUBLICATION FREI FÜR VERÖFFENTLICHUNG ALL RIGHTS RESERVED. ALLE RECHTE VORBEHALTEN THIS DRAWING IS UNPUBLISHED. VERTRAULICHE UNVERÖFFENTLICHTE ZEICHNUNG. COPYRIGHT — By —									
—	—	—	—	—	—	—	—	—	—
CUSTOMER PART NO	PART NO	REV.	PCS.	MATERIAL	SURFACE COLOR	DESCRIPTION			
DIMENSIONS: DIMENSIONEN mm		DWN T.Bersch 27-MAY-98		MATERIAL —		FINISH OBERFLAECHE/FARBE —			
TOLERANCES UNLESS OTHERWISE SPECIFIED: ALLGEMEINTOLERANZEN n. ISO 8015 p.p. DIN 2768 — mH —E DIN 16901 — 140		CHK —		 TE Connectivity					
0 PLC ± — 1 PLC ± — 2 PLC ± — 3 PLC ± — 4 PLC ± — ANGLES/WINKEL ± —		APVD —							
		PRODUCT SPEC PRODUKTSPEZ. —		NAME TAB 2.8 X 0.8 MM TYP A Flachstecker 2.8 x 0.8 mm					
		APPLICATION SPEC VERARBEITUNGSSPEZ. —		SIZE	CAGE CODE	DRAWING NO ZEICHNUNGS-NR.		RESTRICTED TO NUR FUER	
		WEIGHT GEWICHT —		A4	00779	C-964294		—	
				CUSTOMER DRAWING / KUNDENZEICHNUNG			SCALE MASSSTAB —	SHEET BLATT 1 OF 1 VON 1	REV B2