


ENERGIZER L522


9V




Industry Standard Dimensions

This Battery has Underwriters
Laboratories component Recognition

Typical Discharge Performance (21°C)



300Ω (27 mA) Continuous Discharge



Classification:

Lithium 9V

Chemical System:

Lithium-Manganese Dioxide (Li/MnO₂)

Designation:

ANSI-1604LC

Nominal Voltage:

9.0 volts

Operating Temp:

-40°C to 60°C (-40°F to 140°F)

Storage Temp:

-40°C to 60°C (-40°F to 140°F)

Max Discharge :

120 mA continuous *

Typical Weight:

34.4 grams (1.2 oz.)

Typical Volume:

21.4 cubic centimeters (1.3 cubic inch)

Jacket:

Plastic (shipped in foil pouch)

Terminal:

Miniature Snap

Typical Li Content:

1.35 grams (0.048 oz.)

UL Listed:

MH12454

Applications:

This battery best suited for short term applications. **

Shipping:

For complete details, please reference:


Global (except US): Special Provision A45 of the International Air Transport Association Dangerous Goods Regulations

United States: 49-CFR 173.185


* Discharging above 120 millamps (mA) may activate the built-in safety mechanism. This can permanently affect battery performance.

** The battery should remain in the foil pouch until it is put into use. For long term applications, the L522MJ metal jacket version is recommended.

Milliamp-Hours Performance (21°C)



900Ω (9 mA) Continuous Discharge



Important Notice

This datasheet contains typical information specific to products manufactured at the time of its publication.

©Energizer Holdings, Inc. - Contents herein do not constitute a warranty.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Energizer:](#)

[L522FP](#)