



PRODUCT NUMBER
SEE SHEET 3




Copyright FCI.

spec ref	---	dr	Lin-Soe Ngwe	2012/08/31	projection	MM	size	A2	scale	1:1
tolerance std	ASME Y14.5M	eng	Tao Zhan	2014/06/03	chr	-	ecn no	ELX-DG-17834-1	rel level	Released
surface	✓	appr	Collins Lu	2014/06/04	product family	AirMax VSE	cat. no.	10122643	rev	B
TOLERANCES UNLESS OTHERWISE SPECIFIED		FCI		AIRMAX VS2 R.A. RECEPTACLE		ASS'Y, 3 PAIR, 54 POS, 6 IMLA, 12MM		Product - Customer Drw		sheet 1 of 3
linear	0.X ±.3 0.XX ±.10 0.XXX ±.050	angular	0° ±°	www.fci.com	cat. no.		Product - Customer Drw		sheet 1 of 3	

PDS: Rev :B

STATUS:Released

Printed: Jun 04, 2014



RECOMMENDED PCB LAYOUT
FOR DIFFERENTIAL APPLICATIONS
COMPONENT SIDE
(TWO ADJACENT FOOTPRINTS SHOWN)
NOTES 6, 8, & 11

spec ref	---	dr	Lin-Soe Ngwe	2012/08/31	projection	MM	size	A2	scale	1:1
tolerance std	ASME Y14.5M	eng	Tao Zhan	2014/06/03	chr	-	ecn no	ELX-DG-17834-1	rel level	Released
surface	✓	appr	Collins Lu	2014/06/04	product family	AirMax VSE	cat. no.	10122643	rev	B
linear	0.X ±.3 0.XX ±.10 0.XXX ±.050	title	AIRMAX VS2 R.A. RECEPTACLE ASS'Y, 3 PAIR, 54 POS, 6 IMLA, 12MM		dwg no	10122643		sheet 2 of 3		
angular	0° ±°	www.fci.com	cat. no.		Product - Customer Drw					

