








THIS INFORMATION IS CONFIDENTIAL AND PROPRIETARY TO CW INDUSTRIES INCORPORATED AND ITS AFFILIATES. IT MAY NOT BE DISCLOSED TO ANYONE, OTHER THAN CW INDUSTRIES PERSONNEL, WITHOUT WRITTEN AUTHORIZATION FROM CW INDUSTRIES INCORPORATED, SOUTHAMPTON, PENNSYLVANIA USA.

Rating		20A 14VDC		Mounting Hole 	Circuit Diagram 								
Contact Resistance		50m ohm Max.											
Insulation Resistance		DC 500V 100M ohm Min.											
Dielectric Strength		AC 1500V 1 minute											
Operation Temperature		25°C~85°C											
Switch Function		3P SPST ON - OFF Lamp Dependent		<table><tr><td>Thickness</td><td>X</td><td>Y</td></tr><tr><td>0.75~1.5</td><td>23.3+0.1</td><td>11.6+0.1</td></tr><tr><td>1.5~2.5</td><td>23.6+0.1</td><td>11.6+0.1</td></tr></table>		Thickness	X	Y	0.75~1.5	23.3+0.1	11.6+0.1	1.5~2.5	23.6+0.1
Thickness	X	Y											
0.75~1.5	23.3+0.1	11.6+0.1											
1.5~2.5	23.6+0.1	11.6+0.1											
Lamp Type	LED 12VDC 14V w/resistor												

***MATERIAL:**

Frame: Black, Nylon 66 (94-V2)
 Actuator: Red, PC clear (94-V2)
 Waterproof Rubber: Black, Silicone
 Printed: None

*Waterproof: IP65



RoHS Compliant

1 Added Dependent to function & Lamp Type. 3/22/12.

CW INDUSTRIES
 Southampton, Pa. 18966
 Tel 215.355.7080/www.cwind.com

Date Drawn: 2/06/09

Rev. 1

Unit: mm

Checked By: *G. Gold*

Title:
ROCKER SWITCH

CW P/N:
GRB278B802BR1