

LOC	DIST	REVISIONS				
		P	LTR	DESCRIPTION	DATE	DWN
		M		REVISED PER ECR-13-008204	10DEC2013	TM

- 1

0.00076[.000030] MIN GOLD AT POINT OF MEASUREMENT IN THE LOCALIZED GOLD PLATE AREA, 0.00127[.000050] MIN TIN-LEAD IN TIN-LEAD PLATE AREA, 0.00127[.000050] MIN NICKEL UNDERPLATE ON ENTIRE CONTACT.
- 2

WIRE RANGE: 0.5-2mm² [20-14 AWG]
INSULATION RANGE: 3.30-5.08 [.130-.200] DIA.
- 3




DIMENSIONS IN BRACKETS ARE IN INCHES.
- 4

LETTER "P" STAMPED IN THIS LOCATION.
- 5

0.00076[.000030] MIN GOLD AT POINT OF MEASUREMENT IN THE LOCALIZED GOLD PLATE AREA, 0.00127[.000050] MIN TIN IN TIN PLATE AREA, 0.00127[.000050] MIN NICKEL UNDERPLATE ON ENTIRE CONTACT.
- 6

SUPERSEDED BY 1-770005-0
- 7

SUPERSEDED BY 1-770005-1



4	GOLD 5	0.30 [.012] PH BRZ	1-770005-1
	GOLD 5	0.30 [.012] BRASS	1-770005-0
7 4	GOLD 1	0.30 [.012] PH BRZ	770005-4
4	PRE-TIN	0.30 [.012] PH BRZ	770005-3
6	GOLD 1	0.30 [.012] BRASS	770005-2
	PRE-TIN	0.30 [.012] BRASS	770005-1
	FINISH	MATERIAL	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN S. CARPENTER 20MAY03	TE Connectivity	
DIMENSIONS: mm [INCHES]		CHK C. JONES 20MAY03		
	TOLERANCES UNLESS OTHERWISE SPECIFIED:	APVD C. JONES 20MAY03	NAME PIN, UNIVERSAL MATE-N-LOK(TM) II	
	0 PLC ± - 1 PLC ± - 2 PLC ± - 3 PLC ± - 4 PLC ± - ANGLES ± -	PRODUCT SPEC APPLICATION SPEC		
MATERIAL SEE TABLE	FINISH SEE TABLE	WEIGHT -	SIZE A2	CAGE CODE 00779
		CUSTOMER DRAWING	SCALE 4:1	SHEET 1 OF 1
			REV M	