




SECTION B-B'



SECTION A-A'




NOTES

- 1.MATERIAL : BRASS(C26000)
- 2.FINISH : PRE-TIN PLATING
- 3.APPLICABLE HOUSING SOCKET : 68147
- 4.APPLICABLE WIRE SEAL : 49505-9001
- 5.WEDGE BULB INSERTION FORCE : 7.0 Kgf MAX.
WEDGE BULB RETENSION FORCE : 0.5 Kgf MIN.
- 6.APPLICABLE WEDGE BASE CAP : W2.1X9.5d(W16W)
- 7.APPLICABLE WIRE SIZE : 0.5~0.85mm²

<TABLE 1>

354779702	35477-9702
MATERIAL NO.	ORDER NO.



NEW RELEASED
EC NO: KOR2010-0010
DRWNEOK IM 2009/07/29
CHKD:BCYOON 2009/07/30
APPR:YUNS IKK IM 2009/07/30

REV	DESCRIPTION
A	

GENERAL TOLERANCES (UNLESS SPECIFIED)	
mm	INCH
4 PLACES ± ---	± ---
3 PLACES ± ---	± ---
2 PLACES ± 0.2	± ---
1 PLACE ± ---	± ---
ANGULAR ± 1 °	
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS	

DIMENSION STYLE	
MM ONLY	
DRAWN BY	DATE
SMKIM	2005/08/09
CHECKED BY	DATE
BCYOON	2005/08/09
APPROVED BY	DATE
CWLEE	2005/08/09
MATERIAL NO.	
SEE TABLE 1	

SCALE	5:1
DESIGN UNITS	METRIC
THIRD ANGLE PROJECTION	
WEDGE TERMINAL (SPECIAL TYPE)	
MOLEX INCORPORATED	
DOCUMENT NO.	RSD-35477-002
SHEET NO.	1 OF 1