


## ULTRA LOW DROP-LOW NOISE BICMOS VOLTAGE REGULATORS LOW ESR CAPACITORS COMPATIBLE

- INPUT VOLTAGE FROM 2.5V TO 6V
- STABLE WITH LOW ESR CERAMIC CAPACITORS
- ULTRA LOW DROPOUT VOLTAGE (100mV TYP. AT 150mA LOAD, 0.4mV TYP. AT 1mA LOAD)
- VERY LOW QUIESCENT CURRENT (85 $\mu$ A TYP. AT NO LOAD, 170 $\mu$ A TYP. AT 150mA LOAD; MAX 1.5 $\mu$ A IN OFF MODE)
- GUARANTEED OUTPUT CURRENT UP TO 150mA
- WIDE RANGE OF OUTPUT VOLTAGE: 1.25V; 1.35; 1.5; 1.8V; 2V; 2.1V; 2.2V; 2.4V; 2.5V; 2.6V; 2.7V; 2.8V; 2.85V; 2.9V; 3V; 3.1V; 3.2V; 3.3V; 4.7V; 5V
- FAST TURN-ON TIME: TYP. 200 $\mu$ s [C<sub>O</sub>=1 $\mu$ F, C<sub>BYP</sub>= 10nF AND I<sub>O</sub>=1mA]
- LOGIC-CONTROLLED ELECTRONIC SHUTDOWN
- INTERNAL CURRENT AND THERMAL LIMIT
- OUTPUT LOW NOISE VOLTAGE 30 $\mu$ VRMS OVER 10Hz to 100KHz
- S.V.R. OF 60dB AT 1KHz, 50dB AT 10KHz
- TEMPERATURE RANGE: -40°C TO 125°C

### DESCRIPTION

The LD3985 provides up to 150mA, from 2.5V to 6V input voltage.

### SCHEMATIC DIAGRAM



## LD3985 SERIES

## ABSOLUTE MAXIMUM RATINGS

Symbol	Parameter	Value	Unit
$V_I$	DC Input Voltage	-0.3 to 6 (*)	V
$V_O$	DC Output Voltage	-0.3 to $V_I+0.3$	V
$V_{INH}$	INHIBIT Input Voltage	-0.3 to $V_I+0.3$	V
$I_O$	Output Current	Internally limited	
$P_D$	Power Dissipation	Internally limited	
$T_{STG}$	Storage Temperature Range	-65 to 150	°C
$T_{OP}$	Operating Junction Temperature Range	-40 to 125	°C


Absolute Maximum Ratings are those values beyond which damage to the device may occur. Functional operation under these condition is not implied.

(\*) The input pin is able to withstand non repetitive spike of 6.5V for 200ms.

## **THERMAL DATA**

Symbol	Parameter	SOT23-5L	Flip-Chip	Unit
$R_{thj\text{-}case}$	Thermal Resistance Junction-case	81		°C/W
$R_{thj\text{-}amb}$	Thermal Resistance Junction-ambient	255	170	°C/W

## **CONNECTION DIAGRAM** (top view for SOT, top through view for Flip-Chip)




## PIN DESCRIPTION

Pin N° SOT23-5L	Pin N° Flip-Chip	Symbol	Name and Function
1	4	$V_I$	Input Voltage of the LDO
2	2	GND	Common Ground
3	1	$V_{INH}$	Inhibit Input Voltage: ON MODE when $V_{INH} \geq 1.2V$ , OFF MODE when $V_{INH} \leq 0.4V$ (Do not leave floating, not internally pulled down/up)
4	5	BYPASS	Bypass Pin: Connect an external capacitor (usually 10nF) to minimize noise voltage
5	3	$V_O$	Output Voltage of the LDO

## ORDERING CODES

SOT23-5L	Flip-Chip	OUTPUT VOLTAGES
LD3985M125	LD3985J125	1.25 V
LD3985M135	LD3985J135	1.35 V
LD3985M15	LD3985J15	1.5 V
LD3985M18	LD3985J18	1.8 V
LD3985M20	LD3985J20	2.0 V
LD3985M21	LD3985J21	2.1 V
LD3985M22	LD3985J22	2.2 V
LD3985M24	LD3985J24	2.4 V
LD3985M25	LD3985J25	2.5 V
LD3985M26	LD3985J26	2.6 V
LD3985M27	LD3985J27	2.7 V
LD3985M28	LD3985J28	2.8 V
LD3985M285	LD3985J285	2.85 V
LD3985M29	LD3985J29	2.9 V
LD3985M30	LD3985J30	3.0 V
LD3985M31	LD3985J31	3.1 V
LD3985M32	LD3985J32	3.2 V
LD3985M33	LD3985J33	3.3 V
LD3985M47	LD3985J47	4.7 V
LD3985M48	LD3985J48	4.8 V
LD3985M49	LD3985J49	4.9 V
LD3985M50	LD3985J50	5.0 V

## TYPICAL APPLICATION CIRCUIT



## LD3985 SERIES

**ELECTRICAL CHARACTERISTICS FOR LD3985** ( $T_j = 25^\circ\text{C}$ ,  $V_I = V_{O(\text{NOM})} + 0.5\text{V}$ ,  $C_I = 1\mu\text{F}$ ,  $C_{\text{BYP}} = 10\text{nF}$ ,  $I_O = 1\text{mA}$ ,  $V_{\text{INH}} = 1.4\text{V}$ , unless otherwise specified)

Symbol	Parameter	Test Conditions		Min.	Typ.	Max.	Unit
$V_I$	Operating Input Voltage			2.5		6	V
$V_O$	Output Voltage	$I_O = 1\text{ mA}$		-2		2	% of $V_{O(\text{NOM})}$
		$T_j = -40 \text{ to } 125^\circ\text{C}$		-3		3	
$\Delta V_O$	Line Regulation (Note 1)	$V_I = V_{O(\text{NOM})} + 0.5 \text{ to } 6\text{V}$ $T_j = -40 \text{ to } 125^\circ\text{C}$		-0.1		0.1	%/V
		$V_O = 4.7 \text{ to } 5\text{V}$		-0.19		0.19	
$\Delta V_O$	Load Regulation	$I_O = 1\text{ mA to } 150\text{mA}$ (for Flip Chip) $T_j = -40 \text{ to } 125^\circ\text{C}$			0.0004	0.002	%/mA
		$I_O = 1\text{ mA to } 150\text{mA}$ , $T_j = -40 \text{ to } 125^\circ\text{C}$ (for SOT23-5L)			0.0025	0.005	
$\Delta V_O$	Output AC Line Regulation	$V_I = V_{O(\text{NOM})} + 1\text{V}$ , $I_O = 150\text{mA}$ , $t_R = t_F = 30\mu\text{s}$			1.5		$\text{mV}_{\text{PP}}$
$I_Q$	Quiescent Current ON MODE: $V_{\text{INH}} = 1.2\text{V}$	$I_O = 0$			85		$\mu\text{A}$
		$I_O = 0$ $T_j = -40 \text{ to } 125^\circ\text{C}$				150	
		$I_O = 0 \text{ to } 150\text{mA}$				170	
		$I_O = 0 \text{ to } 150\text{mA}$ $T_j = -40 \text{ to } 125^\circ\text{C}$				250	
	OFF MODE: $V_{\text{INH}} = 0.4\text{V}$				0.003		
		$T_j = -40 \text{ to } 125^\circ\text{C}$				1.5	
$V_{\text{DROP}}$	Dropout Voltage (NOTE 1)	$I_O = 1\text{mA}$			0.4		$\text{mV}$
		$I_O = 1\text{mA}$ $T_j = -40 \text{ to } 125^\circ\text{C}$				2	
		$I_O = 50\text{mA}$				20	
		$I_O = 50\text{mA}$ $T_j = -40 \text{ to } 125^\circ\text{C}$				35	
		$I_O = 100\text{mA}$				45	
		$I_O = 100\text{mA}$ $T_j = -40 \text{ to } 125^\circ\text{C}$				70	
		$I_O = 150\text{mA}$				60	
		$I_O = 150\text{mA}$ $T_j = -40 \text{ to } 125^\circ\text{C}$				100	
$I_{\text{SC}}$	Short Circuit Current	$R_L = 0$			600		$\text{mA}$
SVR	Supply Voltage Rejection	$V_I = V_{O(\text{NOM})} + 0.25\text{V} \pm$		$f = 1\text{KHz}$		60	$\text{dB}$
		$V_{\text{RIPPLE}} = 0.1\text{V}$ , $I_O = 50\text{mA}$		$f = 10\text{KHz}$		50	
$I_{O(\text{PK})}$	Peak Output Current	$V_O \geq V_{O(\text{NOM})} - 5\%$		300	550		$\text{mA}$
$V_{\text{INH}}$	Inhibit Input Logic Low	$V_I = 2.5\text{V to } 6\text{V}$ $T_j = -40 \text{ to } 125^\circ\text{C}$				0.4	$\text{V}$
	Inhibit Input Logic High					1.2	
$I_{\text{INH}}$	Inhibit Input Current	$V_{\text{INH}} = 0.4\text{V}$ $V_I = 6\text{V}$				$\pm 1$	$\text{nA}$
$e\text{N}$	Output Noise Voltage	$B_W = 10\text{ Hz to } 100\text{ KHz}$ $C_O = 1\mu\text{F}$			30		$\mu\text{V}_{\text{RMS}}$
$t_{\text{ON}}$	Turn On Time (Note 4)	$C_{\text{BYP}} = 10\text{nF}$			200		$\mu\text{s}$
$T_{\text{SHDN}}$	Thermal Shutdown	Note 5			160		$^\circ\text{C}$
$C_O$	Output Capacitor	Capacitance (Note 6)		1		22	$\mu\text{F}$
		ESR		5		5000	$\text{m}\Omega$

Note 1 – For  $V_{O(\text{NOM})} < 2\text{V}$ ,  $V_I = 2.5\text{V}$

Note 2 – For  $V_{O(\text{NOM})} = 1.25\text{V}$ ,  $V_I = 2.5\text{V}$

Note 3 – Dropout voltage is the input-to-output voltage difference at which the output voltage is 100mV below its nominal value. This specification does not apply for input voltages below 2.5V.


Note 4 – Turn-on time is time measured between the enable input just exceeding  $V_{\text{INH}}$  High Value and the output voltage just reaching 95% of its nominal value

Note 5 – Typical thermal protection hysteresis is  $20^\circ\text{C}$


Note 6 - The minimum capacitor value is  $1\mu\text{F}$ , anyway the LD3985 is still stable if the compensation capacitor has a 30% tolerance in all temperature range.

**TYPICAL PERFORMANCE CHARACTERISTICS** ( $T_J = 25^\circ\text{C}$ ,  $V_I = V_O(\text{NOM}) + 0.5\text{V}$ ,  $C_I = C_O = 1\mu\text{F}$ ,  $C_{\text{BYP}} = 10\text{nF}$ ,  $I_O = 1\text{mA}$ ,  $V_{\text{INH}} = 1.4\text{V}$ , unless otherwise specified)


**Figure 1 : Output Voltage vs Temperature**




**Figure 2 : Output Voltage vs Temperature**




**Figure 3 : Output Voltage vs Temperature**




**Figure 4 : Shutdown Voltage vs Temperature**



**Figure 5 : Shutdown Voltage vs Temperature**




**Figure 6 : Line Regulation vs Temperature**




## LD3985 SERIES


**Figure 7 : Line Regulation vs Temperature**




**Figure 8 : Line Regulation vs Temperature**




**Figure 9 : Load Regulation vs Temperature**




**Figure 10 : Load Regulation vs Temperature**




**Figure 11 : Load Regulation vs Temperature**




**Figure 12 : Quiescent Current vs Temperature**




**Figure 13 : Quiescent Current vs Temperature**




**Figure 14 : Quiescent Current vs Temperature**




**Figure 15 : Supply Voltage Rejection vs Frequency**




**Figure 16 : Load Transient Response**



**Figure 17 : Line Transient Response**




**Figure 18 : START-UP**



## LD3985 SERIES


---

**Figure 19 : TURN-OFF**




## SOT23-5L MECHANICAL DATA

DIM.	mm.			mils		
	MIN.	TYP.	MAX.	MIN.	TYP.	MAX.
A	0.90		1.45	35.4		57.1
A1	0.00		0.10	0.0		3.9
A2	0.90		1.30	35.4		51.2
b	0.35		0.50	13.7		19.7
C	0.09		0.20	3.5		7.8
D	2.80		3.00	110.2		118.1
E	1.50		1.75	59.0		68.8
e		0.95			37.4	
H	2.60		3.00	102.3		118.1
L	0.10		0.60	3.9		23.6




## Flip-Chip5 MECHANICAL DATA

DIM.	mm.			mils		
	MIN.	TYP	MAX.	MIN.	TYP.	MAX.
A	0.835	0.9	0.965	32.874	35.433	37.992
A1	0.21	0.25	0.29	8.268	9.843	11.417
A2	0.625	0.65	0.675	24.606	25.591	26.575
b	0.265	0.315	0.365	10.433	12.402	14.370
D	1.510	1.540	1.570	59.449	60.630	61.811
E	1.16	1.19	1.22	45.669	46.850	48.031
e	0.45	0.5	0.55	17.717	19.685	21.654
e1	0.816	0.866	0.916	32.126	34.094	36.063
f		0.345			13.583	
f1		0.337			13.268	



## Tape &amp; Reel SOT23-xL MECHANICAL DATA

DIM.	mm.			inch		
	MIN.	TYP.	MAX.	MIN.	TYP.	MAX.
A			180			7.086
C	12.8	13.0	13.2	0.504	0.512	0.519
D	20.2			0.795		
N	60			2.362		
T			14.4			0.567
Ao	3.13	3.23	3.33	0.123	0.127	0.131
Bo	3.07	3.17	3.27	0.120	0.124	0.128
Ko	1.27	1.37	1.47	0.050	0.054	0.058
Po	3.9	4.0	4.1	0.153	0.157	0.161
P	3.9	4.0	4.1	0.153	0.157	0.161



Information furnished is believed to be accurate and reliable. However, STMicroelectronics assumes no responsibility for the consequences of use of such information nor for any infringement of patents or other rights of third parties which may result from its use. No license is granted by implication or otherwise under any patent or patent rights of STMicroelectronics. Specifications mentioned in this publication are subject to change without notice. This publication supersedes and replaces all information previously supplied. STMicroelectronics products are not authorized for use as critical components in life support devices or systems without express written approval of STMicroelectronics.

© The ST logo is a registered trademark of STMicroelectronics

© 2003 STMicroelectronics - Printed in Italy - All Rights Reserved  
STMicroelectronics GROUP OF COMPANIES

Australia - Brazil - Canada - China - Finland - France - Germany - Hong Kong - India - Israel - Italy - Japan - Malaysia - Malta - Morocco  
Singapore - Spain - Sweden - Switzerland - United Kingdom - United States.

© <http://www.st.com>