




LOC	DIST	REVISIONS				
		P.	LTR	DESCRIPTION	DATE	DWN
ES	00	A3		REVISED PER ECO-11-005033	09MAY2011	RK
		A4		ECR-11-013206	27JUN2011	D.P
		A5		ECR-13-008246	21MAY2013	CC
						C.W



- 1 MATERIALS:
HOUSING: HIGH TEMPERATURE THERMOPLASTIC, BLACK, UL94 V-0
EXTRACTOR: HIGH TEMPERATURE THERMOPLASTIC, NATURAL (OFF WHITE)
CONTACTS: COPPER ALLOY
RETENTION BARB: COPPER ALLOY
- 2 INTERFACE FINISH:
0.00076 MIN THK GOLD OVER 0.00127 MIN THK NICKEL.
0.00038 MIN THK GOLD OVER 0.00127 MIN THK NICKEL.
- 3 SOLDER TAIL FINISH:
0.00300 MIN THK MATTE LEAD FREE PLATING OVER 0.00127 MIN THK NICKEL.
- 4 RIGHT HOLE IS GLOBAL D-E ORIGIN FOR ALL POSITIONAL TOLERANCES.
LEFT AND RIGHT NON-PLATED THRU HOLES ESTABLISH -E-.
- 5 FINISHED HOLE SIZE. Ø0.15 MAXIMUM ANNULAR RING.

- 6 DATUM -F- IS CONNECTOR SIDE SURFACE OF PCB.
- 7 PORE BLOCKER APPLIED TO CONTACT INTERFACE

OBSOLETE	0.00008 MIN △	4.00	1658912-9
OBSOLETE	0.00008 MIN △	3.18	1658912-8
OBSOLETE	0.00008 MIN △	2.67	1658912-7
OBSOLETE	0.00038 MIN △	4.00	1658912-6
	0.00038 MIN △	3.18	1658912-5
	0.00038 MIN △	2.67	1658912-4
	0.00076 MIN △	4.00	1658912-3
	0.00076 MIN △	3.18	1658912-2
	0.00076 MIN △	2.67	1658912-1
	CONTACT GOLD INTERFACE	TAIL LENGTH	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN D. RINGLER CHK J. McCLELLAN APVD J. McCLELLAN	28OCT2003 29OCT2003 29OCT2003	TE Connectivity	
DIMENSIONS:	mm	TOLERANCES UNLESS OTHERWISE SPECIFIED:	PRODUCT SPEC	NAME	
		0 PLC ±.25 1 PLC ±0.15 2 PLC ±0.13 3 PLC ±.1 4 PLC ±.1	108-2168	SOCKET ASSEMBLY 25 DEGREE DDR II DIMM	
		FINISH	APPLICATION SPEC	240 POSITION, STANDARD FOOTPRINT	
MATERIAL			114-13130	SIZE CAGE CODE DRAWING NO	
			WEIGHT	A100779C=1658912	
			CUSTOMER DRAWING	RESTRICTED TO	
			SCALE	1:1	
			SHEET	1 OF 3	
			REV	A5	


LOC		DIST		REVISIONS			
ES	00	P	LTR	DESCRIPTION	DATE	DWN	APVD
		-		SEE SHEET 1	-	-	-



MINIMUM RECOMMENDED ROW TO ROW SPACING
FOR 4mm THICK MODULE

SCALE 8:1

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN D. RINGLER 28OCT2003	 TE Connectivity					
		CHK J. McCLELLAN 29OCT2003						
		APVD J. McCLELLAN 29OCT2003	NAME SOCKET ASSEMBLY 25 DEGREE DDR II DIMM 240 POSITION, STANDARD FOOTPRINT					
DIMENSIONS:		TOLERANCES UNLESS OTHERWISE SPECIFIED:				PRODUCT SPEC		
mm		0 PLC ±0.25				108-2168		
		2 PLC ±0.15				APPLICATION SPEC		
		3 PLC ±0.013				114-13130		
		4 PLC ±0.013				WEIGHT		
MATERIAL		FINISH				CUSTOMER DRAWING		
						SCALE 1:1 SHEET 2 OF 3 REV A5		



THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN D. RINGLER 28OCT2003	TE Connectivity	
TOLERANCES UNLESS OTHERWISE SPECIFIED:		CHK J. McCLELLAN 29OCT2003		
DIMENSIONS:	mm	APVD J. McCLELLAN 29OCT2003	NAME	
	0 PLC	PRODUCT SPEC	SOCKET ASSEMBLY	
	1 PLC	108-2168	25 DEGREE DDR II DIMM	
	2 PLC	APPLICATION SPEC	240 POSITION, STANDARD FOOTPRINT	
	3 PLC	114-13130	SIZE CAGE CODE DRAWING NO	
MATERIAL	-	WEIGHT	A100779C=1658912	RESTRICTED TO
CUSTOMER DRAWING		SCALE 1:1	SHEET 3 OF 3	REV A5