

REFERENCE SPECIFICATIONS

-NFC 93425 (in compliance with HE 507)

PHYSICAL CHARACTERISTICS

-INSULATOR MATERIAL: THERMOPLASTIC ,UL94V0

-CONTACT MATERIAL: BRASS

-ACCESSORIES: BRASS

-SHELLS: STEEL

ELECTRICAL CHARACTERISTICS

-NOMINAL CURRENT: 30A or 40A

-CONTACT RESISTANCE: <= 7.3 mOhms

-CONTACT/CONTACT : >=1000 V

-CONTACT/GROUND : >=1200 V

-INSULATION RESISTANCE: >=5000 MOhms

ENVIRONMENTAL CHARACTERISTICS

- CLIMATIC CATEGORY: 55/125/21

TEMPERATURE RANGE -55°C TO +125°C

DAMP HEAT STEADY STATE 21 DAYS

SALT SPRAY 24 HOURS

MECHANICAL CHARACTERISTICS

- RETENTION AGAINST TORQUE: - Threaded insert: 0.7 N.m minimum

- Female screw : 0.5 N.m minimum

NOTE RoHS INFORMATION

- The "LF" products meet european union Directives and other country regulations as described in GS-22-008.
- The housing will withstand exposure to 260°C peak temperature for 3.5 seconds in a wave solder application with a 1.6mm minimum thick circuit board. See application notes/procedures if they are available.
- Termination plating spec:
 - Ni 1.27µm+Sn 2.5 to 7.5µm(pure bright)
- Active area plating spec:
 - Ni + Gold
- Shell plating :2 to 4µm Cu + Ni + 3 to 10µmm Sn(pure bright)
- Accessories: Sn pure bright + nickel
- Packaging spec: See GS-14-920

Series

Shell size: **E A B C**
(see sheet 3)

Front accessory definition
(see sheet 2)

blank:without accessory

L :threaded insert M3

O :threaded insert UNC 4-40

V :female screw UNC 4-40

I :female screw M3

Layout of contacts (see sheet 3)

Contacts

P Pin

Termination type

5 Right angle/Europe standard

Plating

00 200 matings/unmatings

43 500 matings/unmatings

PCB accessories definition(see sheet 2)

A :without accessory

H :Metal brackets+harpoons for PCB 2.40mm

G :Metal brackets+harpoons for PCB 1.60mm

M :Metal brackets

Power contacts


00 :Not fitted with power contact (signal contacts always fitted)

30 :Fitted with power contacts 30 Amp.

40 :Fitted with power contacts 40 Amp.

TABLE 1:PCB HOLE DIAMETERS

POWER CONTACTS			ACCESSORIES
30 A	2.00	Ø2.40	Ø3.10
40 A	2.80	Ø3.10	
Max current power	ØA ^{+0.1} / ₀	PCB HOLE ^{+0.1} / _{+/-0.1}	PCB HOLE ^{+0.1} / _{+/-0.1}















www.fciconnect.com		surface	tolerance std	projection	mm
		ISO 1302	ISO 406 ISO 1101	mm	
		TOLERANCES UNLESS OTHERWISE SPECIFIED			
Dr	M PESSON	2005-10-11	ANGULAR	0.X	±0.3
Eng	P LEGARE	2005-10-11	LINEAR	0.XX	±0.1
Chr				0.XXX	±0.05
Appr			Product family		Spec ref
		size		A2	Scale 2:1
		ECN		F09-0092	

rev	ecn no	dr	date	title	sub	part	customer	sheet	total
A	LS05-0113	MPE	2005-10-11	SUB MALE DW EUROPE foot print	full power right angled solder	C01-8639-2312		4	
B	LS06-0208	LGO	2006-12-13						
C	LS07-0213	MPE	2007/11/05						
D	F09-0063	LSA	2009-07-15						
E	F09-0092	LSA	2009/09/16						

PDM-REV-E





STATUS Released

Printed: Apr 28, 2015





1		2	3	4	5	6	7	8
A		B		C		D		E
								
FRONT ACCESSORY		Blank Without		L insert M3 O insert UNC 4.40	V Female screw UNC 4.40 I Female screw M3	Blank Without	L insert M3 O insert UNC 4.40	V Female screw UNC 4.40 I Female screw M3
PCB ACCESSORIES		A Without		A Without	A Without	M Metal brackets	M Metal brackets	M Metal bracket
D		E		F		G		H
								
FRONT ACCESSORY		Blank Without		L insert M3 O insert UNC 4.40	V Female screw UNC 4.40 I Female screw M3	Blank Without	L insert M3 O insert UNC 4.40	V Female screw UNC 4.40 I Female screw M3
PCB ACCESSORIES		G Metal brackets + harpoons for PCB 1.60mm		G Metal brackets + harpoons for PCB 1.60mm	G Metal brackets + harpoons for PCB 1.60mm	H Metal brackets + harpoons for PCB 2.40mm	H Metal brackets + harpoons for PCB 2.40mm	H Metal brackets + harpoons for PCB 2.40mm
SCALE: 4		PDM-REV-E		STATUS Released		Printed: Apr 28, 2015		Released Jun 20, 2015

www.fciconnect.com		surface ISO 1302	tolerance std ISO 406 ISO 1101	projection mm	
TOLERANCES UNLESS OTHERWISE SPECIFIED		size		Scale	
Dr	M PESSON 2005-10-11	ANGULAR	0.X ±0.3	A2	2:1
Eng	P LEGARE 2005-10-11	LINEAR	0.XX ±0.1		
Chr		0° ±2°	0.XXX ±0.05	ECN	F09-0092
Appr		Product family		Spec ref	
FCI		SUB MALE DW EUROPE foot print full power right angled solder		eng no	Rev.
				C01-8639-2312	E





2V2

LAYOUT AND CONNECTOR DIMENSIONS
For PCB hole diameters see table 1 sheet 1


3V3

LAYOUT AND CONNECTOR DIMENSIONS
For PCB hole diameters see table 1 sheet 1

3W3




SIDE VIEW FOR ALL LAYOUTS




www.fciconnect.com		surface ISO 1302	tolerance std ISO 406 ISO 1101	projection mm
		TOLERANCES UNLESS OTHERWISE SPECIFIED		
Dr	M PESSON	2005-10-11	ANGULAR	size A2
Eng	P LEGARE	2005-10-11	LINEAR	Scale 2:1
Chr			0° ±2°	ECN F09-0092
Appr			Product family	Spec ref

FCI	title SUB MALE DW EUROPE foot print	part no C01-8639-2312	Rev. E
	full power right angled solder	CUSTOMER	

5W5 LAYOUT AND CONNECTOR DIMENSIONS For PCB hole diameters see table I sheet I



8W8 LAYOUT AND CONNECTOR DIMENSIONS For PCB hole diameters see table I sheet I



www.fciconnect.com		surface ISO 1302	tolerance std ISO 406 ISO 1101	projection mm
		TOLERANCES UNLESS OTHERWISE SPECIFIED		
Dr	M PESSON	2005-10-11	ANGULAR	size A2
Eng	P LEGARE	2005-10-11	LINEAR	Scale 2:1
Chr			0° ±2°	ECN F09-0092
Appr			Product family	Spec ref

Title SUB MALE DW EUROPE foot print full power right angled solder		Part no C01-8639-2312	Rev. E
--	--	--------------------------	-----------