

9987 Hook-up/Lead - UL AWM Style 1061

 	For more information please call 1-800-Belden1 <u>See Put-ups and Colors</u>
--	---

Description:

Tinned copper conductor, semi-rigid PVC insulation (solid conductors suitable for wire wrap applications).

PHYSICAL CHARACTERISTICS:

CONDUCTOR:

Number of Conductors	1
Total Number of Conductors	1
AWG	30
Stranding	7x38
Conductor Material	TC - Tinned Copper

INSULATION:

Insulation Material	PVC - Polyvinyl Chloride
Insulation Thickness	.010 in.

OVERALL:

Overall Nominal Diameter	.032 in.
--------------------------	----------

APPLICABLE SPECIFICATIONS AND AGENCY COMPLIANCE:

APPLICABLE STANDARDS:

UL AWM Style	1061
UL Rating	300 V RMS, 80°C
CSA Type	AWM I, A/B
CSA Rating	300 V RMS, 80°C
EU CE Mark (Y/N)	Yes
EU RoHS Compliant (Y/N)	Yes
EU RoHS Compliance Date (mm/dd/yyyy):	10/01/2005

FLAME TEST:

UL Flame Test	VW-1
---------------	------

PLENUM/NON-PLENUM:

Plenum (Y/N)	N
--------------	---

PUT-UPS AND COLORS:

9987 Hook-up/Lead - UL AWM Style 1061

Item	Description	Put-Up (ft.)	Ship Weight (lbs.)	Jacket Color	Notes
9987 002100	30 STR PVC RED	100	0.1	RED	
9987 0021000	30 STR PVC RED	1000	1	RED	
9987 007100	30 STR PVC VIO	100	0.1	VIOLET	
9987 0071000	30 STR PVC VIO	1000	1	VIOLET	
9987 0081000	30 STR PVC GRY	1000	1	GRAY	
9987 009100	30 STR PVC WHT	100	0.1	WHITE	
9987 0091000	30 STR PVC WHT	1000	1	WHITE	
9987 010100	30 STR PVC BLK	100	0.1	BLACK	
9987 0101000	30 STR PVC BLK	1000	1	BLACK	

Revision Number: 1 Revision Date: 11-17-2006

© Copyright 2006 Belden, Inc
All Rights Reserved.

Although Belden ("Belden") makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described herein are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with the following environmental regulations: California Proposition 65 Consent Judgment For Wire & Cable Mfgs.(San Francisco Superior Court Nos. 312962 And 320342); EU RoHS (Directive 2002/95/EC, 27-Jan-2003);Material manufactured prior to the compliance date may still be in stock at Belden facilities and in our Distributor's inventory. EU ELV (Directive 2000/53/EC, 18-Sept-2000); EU WEEE (Directive 2002/96/EC, 27-Jan-2003); And EU BFR (Directive 2003/11/EC, 6-Feb-2003). The information provided in this Product Disclosure, and the identification of materials listed as reportable or restricted within the Product Disclosure, is correct to the best of Belden's knowledge, information and belief at the date of its publication. The information provided in the Product Disclosure is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. This Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.

Belden declares this product to be in compliance with EU LVD (Low Voltage Directive 73/23/EEC), as amended by directive 93/68/EEC.