

# SMD Seam Sealing Crystals

## 3.2 x 2.5 x 0.7 mm 7M Series



### Features

- Extremely small SMD type crystal units.
- High precision and high frequency stability.
- Extremely good for reducing EMI effect.
- The best choice of Bluetooth, wireless communication set,
- DSC, PDA, and mobile phone.
- RoHS Compliant / Pb Free.




### Electrical Specifications

| Item / Type                    | 7M                                      |
|--------------------------------|-----------------------------------------|
| Frequency Range                | 10 ~ 114.285 MHz                        |
| Frequency Tolerance (at 25 °C) | ± 30 ppm, or specify                    |
| Frequency Stability            | ± 30 ppm ( - 20 ~ + 70 °C ), or specify |
| Operating Temperature Range    | - 40 ~ + 85 °C                          |
| Shunt Capacitance (C0)         | 3 pF Max.                               |
| Drive Level                    | 1 ~ 100 μW (50 μW typical)              |
| Load Capacitance               | 18 pF, or specify                       |
| Aging (at 25 °C)               | ± 3 ppm / year Max.                     |
| Storage Temperature Range      | - 40 ~ + 85 °C                          |

### Equivalent Series Resistance(ESR)

| Fundamental      |            |
|------------------|------------|
| 10 ~ 16 MHz      | 100 Ω Max. |
| 16 ~ 20 MHz      | 80 Ω Max.  |
| 20 ~ 114.285 MHz | 60 Ω Max.  |

### Dimensions



Units: mm

Remark : Specification subject to change without prior notice. Please confirm with our sales.

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

## [TXC Corporation:](#)

[7M-12.000MAAJ-T](#) [7M-12.000MEEQ-T](#) [7M-12.288MAAJ-T](#) [7M-12.288MEEQ-T](#) [7M-13.000MAAJ-T](#) [7M-13.560MAAJ-T](#) [7M-13.560MEEQ-T](#) [7M-14.31818MAAJ-T](#) [7M-16.000MAAJ-T](#) [7M-16.000MEEQ-T](#) [7M-16.384MAAJ-T](#) [7M-16.384MEEQ-T](#) [7M-16.9344MAAJ-T](#) [7M-18.432MAAJ-T](#) [7M-18.432MEEQ-T](#) [7M-19.200MAAJ-T](#) [7M-19.200MEEQ-T](#) [7M-20.000MAAJ-T](#) [7M-20.000MEEQ-T](#) [7M-24.000MAAJ-T](#) [7M-24.000MEEQ-T](#) [7M-24.576MAAJ-T](#) [7M-24.576MEEQ-T](#) [7M-25.000MAAJ-T](#) [7M-25.000MEEQ-T](#) [7M-26.000MAAJ-T](#) [7M-26.000MEEQ-T](#) [7M-27.000MAAJ-T](#) [7M-27.000MEEQ-T](#) [7M-27.120MAAJ-T](#) [7M-27.120MEEQ-T](#) [7M-30.000MAAJ-T](#) [7M-30.000MEEQ-T](#) [7M-32.000MAAJ-T](#) [7M-32.000MEEQ-T](#) [7M-36.000MAAJ-T](#) [7M-36.000MEEQ-T](#) [7M-38.400MAAJ-T](#) [7M-38.400MEEQ-T](#) [7M-40.000MAAJ-T](#) [7M-40.000MEEQ-T](#) [7M-48.000MAAJ-T](#) [7M-48.000MEEQ-T](#) [7M-10.000MAAJ-T](#) [7M-22.000MEEQ-T](#) [7M-28.63636MEEQ-T](#) [7M-44.000MEEQ-T](#) [7M-50.000MAAJ-T](#) [7M-36.000MAHV-T](#) [7M-16.000MAHV-T](#) [7M-24.000MAHV-T](#) [7M-10.000MAHV-T](#) [7M-13.000MAHV-T](#) [7M-32.000MAHV-T](#) [7M-38.400MAHV-T](#) [7M-50.000MAHV-T](#) [7M-26.000MAKV-T](#) [7M-26.000MAHV-T](#) [7M-27.120MAHV-T](#) [7M-19.200MAHV-T](#) [7M-25.000MAKV-T](#) [7M-27.000MAKV-T](#) [7M-37.400MAHV-T](#) [7M-25.000MAHV-T](#) [7M-40.000MAKV-T](#) [7M-40.000MAHV-T](#) [7M-27.000MAHV-T](#) [7M-24.000MAKV-T](#) [7M-20.000MAHV-T](#) [7M-12.288MAHV-T](#) [7M-30.000MAHV-T](#) [7M-48.000MAHV-T](#) [7M-12.000MAHV-T](#)