



LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
AJ	00		T2	REV PER ECO 06-029805	2/6/2007	DW	JL



RECOMMENDED STRIP LENGTH

- ⚠ 1 USE CRIMP TOOL: 220190-1 OR PRO-CRIMPER
2. USE INSTRUCTION SHEET 408-9090
3. DIELECTRIC MUST WITHSHAND A 5 LB PUSH OUT FORCE
- ⚠ 4 SPECIAL PACKAGING
- ⚠ 5 SUPERSEDED BY 221199-2
- ⚠ 6 CUSTOM CABLE:
CENTER CONDUCTOR = Ø.016
DIELECTRIC = Ø.070
JACKET = Ø.110
- ⚠ 7 CUSTOM CABLE:
CENTER CONDUCTOR = Ø.016
DIELECTRIC = Ø.075
JACKET = Ø.120

SUPERSEDED BY 413760-3		OBSOLETE	RG-59/U,59A/U & 59B/U	58085-1	-	-	9-50428-0	221200-3	221202-2	9-221199-1						
		OBSOLETE	BELDEN 9248, MADISON 18AWG	58086-1	-	-	9-50427-0	3-221200-2	221202-1	9-221199-0						
		OBSOLETE	C&M CABLE 25785	58304-4	-	-	3-328666-6	221200-6	221202-4	221199-9						
	7	OBSOLETE	CUSTOM CABLE	58304-5	1-222001-6	414932-3	3-328666-9	221200-9	221202-3	221199-8						
	6	OBSOLETE	CUSTOM CABLE	58304-1	222001-8	227194-2	9-328666-0	221200-9	221202-3	221199-7						
		OBSOLETE	AT&T 735A	58174-1	-	-	9-328666-2	221200-9	221202-3	221199-6						
			RG-179	58304-1	222001-8	227194-2	9-328666-0	2-221200-0	221202-3	221199-5						
	5	4	OBSOLETE	RG-59/U,59A/U & 59B/U	58085-1	-	-	9-50428-0	221200-3	221202-2	221199-4					
			OBSOLETE	BELDEN 8218	58174-1	-	-	9-329461-0	221200-9	221202-3	221199-3					
			OBSOLETE	RG-59/U,59A/U & 59B/U	58085-1	-	-	9-50428-0	221200-3	221202-2	221199-2					
			BELDEN 9248, MADISON 18AWG	58086-1	-	-	9-50427-0	3-221200-2	221202-1	221199-1						
			FOR USE WITH CABLE	DIE SET	1	5	TUBING, METAL QTY=1	4	TUBING, PLASTIC QTY=1	3	FERRULE QTY=1	2	CONTACT QTY=1	1	JACK ASSEMBLY QTY=1	PART NUMBER