






KIT P/No.	HOUSING QTY	CONTACT QTY	P.C.B. Thk.	PRODUCT TYPE
88990-301/301LF	1	3	1.6mm	HEAT STAKE S.T.B.
88990-303/303LF	1	3	2.4mm	HEAT STAKE S.T.B.
88990-304/304LF	1	1	1.6mm	HEAT STAKE S.T.B.
88990-901/901LF	1	2	1.6mm	HEAT STAKE S.T.B.
88990-401/401LF	1	3	1.6mm	PRESS-PEG S.T.B.
88990-402/402LF	1	3	2.4mm	PRESS-PEG S.T.B.
88990-403/403LF	1	2	1.6mm	PRESS-PEG S.T.B.
88990-404/404LF	1	1	1.6mm	PRESS-PEG S.T.B.
88990-411/411LF	1	3	FLEXIBLE	PRESS-PEG P.F.
88990-412/412LF	1	2	FLEXIBLE	PRESS-PEG P.F.
88990-413/413LF	1	1	FLEXIBLE	PRESS-PEG P.F.
88990-803/803LF	1	1	2.4mm	HEAT STAKE S.T.B.
88990-903/903LF	1	2	2.4mm	HEAT STAKE S.T.B.



RECOMMENDED HOLE PATTERN,
COMPONENT SIDE.

- 1 Indicated holes are unplated
- 2 For contact used in this kit
count one contact as two lines;
3. FOR LEAD FREE PART NUMBERS, ADD AN "LF" SUFFIX,
EXAMPLE : 88990-301LF
- 4.THESE PRODUCTS WHERE THE PART NUBER ENDS IN "LF" MEET
THE EUROPEAN UNION DIRECTIVES AND OTHER COUNTRY
REGULATIONS AS DESCRIBED IN GS-22-008

mat'l. code				tolerances unless otherwise specified				CUSTOMER COPY		 ELECTRONICS www.fcbconnect.com	
lir	ecn	dr	date	linear	 mm			titl	RA RECEPTACLE MINI COAX KIT		
H	H50183	RV	960312								
H	B10105	RR	011210								
K	9607-0872	Cent	070228								
L	0607-0276	Cent	07/04/07								
					D Andrews	920507		product family	METRAL (tm)		code
					engr	D Andrews	920507	size	dwg no		213
F	H50076	DAN	950203	chr	P Schalk	960312	scale	A2		88990	sheet
G	H50770	RV	960312	app	H. Coolmans	960312	5:1				1 of 1
sheet index	revision sheet	L	1								