

T&B® Fittings

**T&B Catalog Number:****EFC125****UPC Number:**

78621078964

Description:

1 1/4" Black Corrugated PVC flexible tubing. For use with Bullet®; Liquidtight Fittings.

Status:

Active

Features

Maximum flexibility in tight applications.

Extremely fast installation

Liquidtight with specified fittings.

Good tensile strength provides excellent pullout protection and smooth inner diameter allows easy wire pulling.

General

Material	PVC
Color	Black
Conduit Size (inches)	1 1/4
Recommended industrial applications	Protection of fiber optic cable, installation of instrumentation and control cable, indoor and outdoor lighting, packaging equipment, marine and shipboard wiring, and flexing-component wiring protection on robots, graphic arts equipments, etc.

Dimension Information

I.D. - Minimum (inches)	1.380
I.D. - Maximum (inches)	1.410
O.D. - Minimum (inches)	1.630
O.D. - Maximum (inches)	1.660

Packaging

T&B Order Multiple	100
Package in Units	100
T&B Sold in UOM	Feet
T&B Weight Per UOM	21.4 lbs. per 100

Application Support

Guide to Nonmetallic Conduit Applications Available on Website

XTRAFLEX System Specifications Available on Website

Notes

*Note	OEM Grade U.L. Recognized
**Note	Broad operating temperature range - 18°C to +60°C; C (-2°F to +140°F); F
***Note	Flammability rating VW-1 (vertical wire) UL 224.

Certifications

RoHS Compliance Yes

Certifications

File Nbr:

E 96548

XTRA FLEX® System —

Conduit, Tubing, Fittings for Non-Metallic Liquidtight Conduit Material — PVC



Maximum flexibility for tight applications!

Corrugated Flexible Non-Metallic Tubing



- OEM grade — UL Recognized
- PVC material
- Black color standard
- Extremely fast installation
- Liquidtight with specified fittings
- Good tensile strength provides excellent pullout protection
- Smooth inner diameter allows easy wire pulling
- Broad operating temperature range: 18° C to +60° C (-2° F to +140° F).
- Flammability Rating VW-1 (Vertical Wire) UL224

Recommended industrial applications

- Protection of fiber optic cable
- Installation of instrumentation and control cable
- Indoor/outdoor lighting
- Packaging equipment
- Marine and shipboard wiring
- Flexing component wiring protection on robots, graphic arts equipment, etc.



CAT. NO.	CONDUIT SIZE	I.D. (IN.)		O.D. (IN.)	
		MIN.	MAX.	MIN.	MAX.
EFC025*	1/4"	.390	.405	.560	.575
EFC038	5/16"	.484	.504	.690	.710
EFC050	3/8"	.622	.642	.820	.840
EFC075	1/2"	.820	.840	1.030	1.050
EFC100	1"	1.041	1.066	1.290	1.315
EFC125	1 1/4"	1.380	1.410	1.630	1.660
EFC150	1 1/2"	1.575	1.600	1.865	1.900
EFC200	2"	2.020	2.045	2.340	2.375

* Not CSA Certified.
Underwriters Recognized
UL File No. 96548

CSA File No. 087241
See technical data next page.
Use with Bullet® Liquidtight Fittings.

CAT. NO. LTC —	AVAILABLE COLORS	
	COLOR OF CONDUIT	
W/O SUFFIX	Black	
-1	Orange	
-2	Blue	