


FINISHED WIRE DATA		
CONDUCTORS	WIRE AWG	24 AWG SOLID
	MATERIAL	SOLID BARE COPPER
INSULATION	MATERIAL	FEP/POLYOLEFIN
JACKET	MATERIAL	FR PVC

COLOR CODE

PAIR COLOR CODE

- 1 WHT/BLU
- 2 WHT/ORG
- 3 WHT/GRN
- 4 WHT/BRN



LEGEND TO BE REPEATED EVERY 24"

TE CONNECTIVITY 610 SERIES 4/24 AWG T256 CMP C(UL)US ETL VERIFIED TIA-568-C.2 CAT 6 XXXX FT



LOC	DIST	REVISIONS				
		P	LTR	DESCRIPTION	DATE	DWN
HM	00		L	REV ECO-12-013616	30JUL2012	GG

- 1 SEQUENTIAL FOOTAGE RETURNED TO ZERO FOR EACH LENGTH. ON PUTUP LENGTHS 3000 FT OR LESS.
- 2 MATERIALS ARE SELECTED BASED ON THEIR ABILITY TO CONFORM TO UL 444 LATEST ISSUES.
3. INSULATION COLORS SHALL BE BLUE, ORANGE, GREEN, BROWN AND WHITE. THE INSULATION COLOR MAY BE TRANSLUCENT.
- 4 XX = JACKET COLOR - BL = BLUE, WT = WHITE, GY = GRAY, GN = GREEN, YL = YELLOW, OR = ORANGE, RD = RED, VT = VIOLET, BK = BLACK.
- 5 PRINT COLOR SHALL BE BLACK OR DARK BLUE, EXCEPT. WHITE ON BLACK JACKET.
- 6 DATE CODE.
7. GOVERNING SPECIFICATIONS - LATEST REVISIONS
NEC 800
UL444 CMP
TIA 568-C.2 CAT 6
- 8 REPLACE "02" FOR THE FOLLOWING FOOTAGES:
04=2000', 05=2500', CALL FOR ADDITIONAL OPTIONS.

CATALOG NUMBER	WEIGHT		PACKAGING
	LBS/KFT	KG/KM	
TE610P-XX02	29	43	1,000' REEL
TE610P-XXII	29	43	1,000' REELEX BOX



THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN L. HALL 05DEC2007	TE Connectivity			
DIMENSIONS: INCHES		CHK J. GENIAC 11DEC2007	NAME CABLE, SERIES 610, 4UTP, 24 AWG, CMP			
		APVD J. GENIAC 11DEC2007				
	TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± - 1 PLC ± - 2 PLC ± .02 3 PLC ± .005 4 PLC ± - ANGLES ± - FINISH -	PRODUCT SPEC -	SIZE -			
		APPLICATION SPEC -	CAGE CODE -			
MATERIAL -	2	WEIGHT -	A2	00779	DRAWING NO C=1933047	RESTRICTED TO -
CUSTOMER DRAWING			SCALE NTS	SHEET 1 of 1	REV L	