



Copyright FCI.

PRODUCT NO.
73725

PRODUCT NUMBER CODE

HOUSING COLOR OPTION

- 0-WHITE
- 1-BLACK

SENSOR CONTACT OPTION

- 0-WITH SENSOR CONTACT
- 1-WITHOUT SENSOR CONTACT

SHIELD PLATING OPTION

- 1- 1.25μm MINIMUM NICKEL UNDERPLATE & 2.5μm MINIMUM BRIGHT TIN OVER ALL AREA. (HOLD DOWN STYLE "A")
- 2- 1.25μm MINIMUM NICKEL UNDERPLATED OVER ALL; 2.5 μm MINIMUM BRIGHT TIN PLATED ON HOLD DOWN AREA ONLY. (HOLD DOWN STYLE "B")
- 3- 1.25μm MINIMUM NICKEL UNDERPLATED OVER ALL; 2.5 μm MINIMUM BRIGHT TIN PLATED ON HOLD DOWN AREA ONLY. (HOLD DOWN STYLE "A")
- 4- 1.25μm MINIMUM NICKEL UNDERPLATED & 2.5μm MINIMUM BRIGHT TIN OVER ALL AREA. (HOLD DOWN STYLE "B")
- 5- 1.25μm MINIMUM NICKEL UNDERPLATED OVER ALL; 2.5μm MINIMUM BRIGHT TIN PLATED ON HOLD DOWN AREA ONLY. (HOLD DOWN STYLE "C")
- 6- 1.25μm MINIMUM NICKEL ONLY. (HOLD DOWN STYLE "A")
- 7- 1.25μm MINIMUM NICKEL UNDERPLATED & 2.5 μm MINIMUM MATTE TIN PLATED OVER ALL. (HOLD DOWN STYLE "A")
- 8- 1.25μm MINIMUM NICKEL UNDERPLATED & 2.5 μm MINIMUM MATTE TIN PLATED ALL AREA. (HOLD DOWN STYLE "B")
- 9- 1.25μm MINIMUM NICKEL UNDERPLATED OVER ALL; 2.5 μm MINIMUM MATTE TIN PLATED ON HOLD DOWN AREA ONLY. (HOLD DOWN STYLE "D")
- S- 1.25μm MINIMUM NICKEL ONLY; (HOLD DOWN STYLE "A"). HIGH PERFORMANCE MATERIAL FOR 12,000 DURABILITY CYCLES
- A- 1.25μm MINIMUM NICKEL PLATED OVER ALL. 2.5 μm MINIMUM MATTE TIN PLATED ON HOLD DOWN AREA ONLY. (HOLD DOWN STYLE "B")

TERMINAL OPTION

50u" NI UNDERPLATE; 30u" GXT CONTACT AREA, 100u" TIN TAIL AREA;

- 0- DIM "A": 2.29 (TERMINAL TAIL LENGTH);
- 1- DIM "A": 3.71 (TERMINAL TAIL LENGTH);


NOTES:

- MATERIAL:
CONTACTS: COPPER ALLOY
SHIELD: COPPER ALLOY
HOUSING: UL 94V-0 THERMOPLASTIC, COLOR: SEE PRODUCT CODE
- PLATING:
CONTACTS: GOLD FLASH OVER PALLADIUM NICKEL (0.76μm MINIMUM) IN CONTACT AREA; 2.5 μm TIN MINIMUM IN SOLDER TAIL AREA.
1.27 μm MINIMUM NICKEL UNDERPLATE OVER ALL SURFACES.
SHIELD: SEE PRODUCT NUMBER CODE.
(THE PLATING MEASURE POINT ON THE SHIELD HOLD DOWN AREA ONLY).
- DATUMS & BASIC DIMENSIONS TO BE DETERMINED BY CUSTOMER
- RECOMMENDED PCB BOARD THICKNESS IS 1.00 ~ 1.60mm EXCEPT 73725-1191BLF; 73725-1191BLF CAN BE USED FOR THE PCB BOARD THICKNESS 2.30 ~ 2.65mm.
- MAXIMUM PANEL THICKNESS TO BE 2.67mm IF MOUNTED BEHIND PANEL
- METAL SHELL SLIVER 0.20 MAX.
- NI PLATING DOES NOT COMPLY WITH THE USB STANDARDS (TO BE CONTINUED)

LEAD FREE OPTION
SEE NOTE 9


PACKAGING OPTION
B - TUBE
R - TAPE&REEL

SENSOR CONTACT



5.76


5.12±0.10



12.50±0.10


POS. #1

WITH SENSOR CONTACT



FRONT OF CONNECTOR



PC BOARD MOUNTING DIMENSIONS FOR 5 PIN



FOR 73725-X0X0B
HOLD DOWN STYLE "A"

mat'l code				tolerance unless otherwise specified		CUSTOMER COPY		FCI	
rev.	ecn	no.	dr	date	linear	.0 ± .30	projection	title	www.fciconnect.com
AB	N09	0202	R.B	2009/06/25		.00 ± .20		USB UP-RIGHT	
AC	N10	0128	A.ZH	05/14/2010		.000± 0.10		RECEIPT	
AD	ELX-N-14592		A.ZH	06/25/2012	angles	± 2°			
AE	ELX-N-13462		A.ZH	11/14/2012	dr	PAMP	5/20/97	product family	USB
AF	ELX-N-14592		J.HAN	06/10/2013	enrg	R Y LIU	5/20/97	code	NT
AG	ELX-N-21594		LQ	06/04/2015	chr	R Y LIU	5/20/97	size	dwg no.
					appd	JENN TSAO	5/20/97	scale	73725
sheet	revision	AG							
index	sheet	1-4							

13. DATUM OF CUSTOMER'S PCB LAYOUT.



FOR 73725-X1X0B


6




Copyright FCI.

PRODUCT NO.


73725




PC BOARD MOUNTING DIMENSIONS FOR 4 PIN




SECTION A-A



WITH SENSOR CONTACT
FOR 73725-X0X0B
HOLD DOWN STYLE "B"



WITHOUT SENSOR CONTACT
FOR 73725-X1X0B
HOLD DOWN STYLE "B"





WITHOUT SENSOR CONTACT
FOR 73725-X191XLF
HOLD DOWN STYLE "D"

mat'l code				tolerance unless otherwise specified		CUSTOMER COPY		FCI www.fciconnect.com	
rev.	ecn	no.	dr	date	linear	.0 ± .30	projection	title USB UP-RIGHT RECEPT	
AG						.00 ± .20			
					angles	.000 ± 0.10		product family USB	
						± 2°			
			dr	PETER	5/20/97	unit	mm	size	
			enr	JOHN WEN	5/20/97	scale	A3		
			chr	JOHN WEN	5/20/97			73725	
			appd	JENN TSAO	5/20/97				
sheet	revision							3 OF 4	
index	sheet								


PRODUCT NO.

73725



WITHOUT SENSOR CONTACT
FOR 73725-X1X0B

HOLD DOWN STYLE "C"



mat'l code				tolerance unless otherwise specified		CUSTOMER COPY		FCI www.fciconnect.com	
rev.	ecn	no.	dr	date	linear	.0 ± .30	projection	title USB UP-RIGHT RECEPT	
AG						.00 ± .20	⊕		
					angles	.000± 0.10		product family USB	
					dr	PETER 01/12/99	unit	code	
					enr	R Y LIU 01/12/99	mm	NT	
					chr	R Y LIU 01/12/99	scale	sheet	
					appd	JENN TSAO 01/12/99		4 OF 4	
sheet revision									
index	sheet								