

FREEPORT ILLINOIS, U.S.A
A DIVISION OF HONEYWELL
FED. MFG. CODE 91929

MINIATURE PRECISION LIMIT SWITCH

924CE2-T3

924CE2-T3

N

DRAWING
NUMBER

$$\frac{2}{x}$$

ANS

REPLACES

PR 14729

CHECK

MECH

工

CHECK


98 130

20

51


FO-52848-A

DRAWN



NOTES


- 1 - ZINC HOUSING FINISHED WITH GRAY PAINT
2 - MAKE BEFORE BREAK CIRCUITRY



CIRCUIT DIAGRAM

THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF MICRO SWITCH, A DIVISION OF HONEYWELL. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE APPROVAL OF MICRO SWITCH.

THIRD ANGLE PROJECTION



CHARACTERISTICS

OPERATING FORCE - - - - - 5.1 LB MAX

ELECTRICAL DATA

CONTACT ARRANGEMENT
S P D T D B

10A - 250 VAC
1/3 HP - 125 OR 250 VAC



OVERTRAVEL - - - - - .020 MIN

SCALE FULL

DO NOT SCALE PRINT

TOLERANCES

APPLY TO DESIGN UNITS. CONVERSIONS ARE ONLY FOR
REFERENCE. UNLESS NOTED, TOLERANCES ARE $\pm$

	DIM. mm	TOL. mm/in	DIM. in	TOL. mm/in
NO PLACES	X	1/04		
ONE PLACE	X,X	0.4/016	X,X	0.8/008
TWO PLACES	X,XX	0.15/008	X,XX	0.36/015
THREE PLACES			X,XXX	0.13/006

DESIGN UNITS ☐ BI METRIC ☐

US CUSTOMARY

WEIGHT