

Terminal Part Number: 13595182
Surface Plating: CR
Material Thickness [mm]: 1,40
Cross Section [mm²]: 5,00

*This document is non-contractual
and for information only.*



*For more information, please
consult your local sales office*

Cable Type codes: 1005
Crimp Process: (C) CRIMP ONLY - TERMINAL IS APPLIED CRIMP ONLY
Insulation Range Φ[mm]: 3,70 - 4,07
Seal(s): NONE

Cable type / seal	Arrangement	Nominal Insul. diam [mm]	Tear-out force [N]	CCH [mm]	Tol CCH [mm]	CCW [mm]	Tol CCW [mm]	ICH [mm]	Tol ICH [mm]	ICW [mm]	Tol ICW [mm]
1005 5,00		3,89	290	4,70	0,05	7,85	0,20	6,60	0,20	8,20	0,20

Cable type code legend:

1005:
Industry Designator: SAE
Conductor Material: COPPER
Conductor Plating: NONE
Insul. Material: PVC, PVDF, XLPE
Insul. Wall Designator: THIN



Crimp Information Sheet

DELPHI

Terminal Part Number: 13595182
Surface Plating: CR
Material Thickness [mm]: 1,40
Cross Section [mm²]: 10,00 | 6,00

*This document is non-contractual
and for information only.*

*For more information, please
consult your local sales office*

Cable Type codes: 2010
Crimp Process: (C) CRIMP ONLY - TERMINAL IS APPLIED CRIMP ONLY
Insulation Range Φ [mm]: 3,80 - 7,10
Seal(s): NONE

Cable type / seal	Arrangement	Nominal Insul. diam [mm]	Tear-out force [N]	CCH [mm]	Tol CCH [mm]	CCW [mm]	Tol CCW [mm]	ICH [mm]	Tol ICH [mm]	ICW [mm]	Tol ICW [mm]
2010 10,00		6,80	1000	5,00	0,05	7,50	0,20	8,30	0,20	8,30	0,20
2010 6,00		4,05	320	5,35	0,05	7,60	0,20	6,20	0,20	7,60	0,20

Cable type code legend:

2010: ACW0219, FIAT T2 FLRY, FL RENAULT R1, FL RENAULT R3, FLR
(AGP0219), FLR2X-A, FLR4Y-A, FLR9Y, FLRX-B, FLRY-A, FLRYB, FLRY-B



Industry Designator: DIN

Conductor Material: COPPER

Conductor Plating: NONE

Insul. Material: PA, POLYOLEFIN, PP, PVC, SYNTHRESIN, XLCOPOLY, XLPBT, XLPE,
XLPE/PVDF, XLPVC

Insul. Wall Designator: THIN



Crimp Information Sheet

DELPHI

Terminal Part Number: 13595182
Surface Plating: CR
Material Thickness [mm]: 1,40
Cross Section [mm²]: 10,00 | 6,00

*This document is non-contractual
and for information only.*



*For more information, please
consult your local sales office*

Cable Type codes: 2011
Crimp Process: (C) CRIMP ONLY - TERMINAL IS APPLIED CRIMP ONLY
Insulation Range Φ [mm]: 4,40 - 5,70
Seal(s): NONE

Cable type / seal	Arrangement	Nominal Insul. diam [mm]	Tear-out force [N]	CCH [mm]	Tol CCH [mm]	CCW [mm]	Tol CCW [mm]	ICH [mm]	Tol ICH [mm]	ICW [mm]	Tol ICW [mm]
2011 10,00		5,00	1000	5,00	0,05	7,50	0,20	9,20	0,20	8,60	0,20
2011 6,00		5,05	320	5,35	0,05	7,60	0,20	6,20	0,20	7,60	0,20

Cable type code legend:

2011: FL33X, FLK, FLY, FLYKW, IH WIRE
Industry Designator: DIN
Conductor Material: COPPER
Conductor Plating: NONE
Insul. Material: P/EST, PE, PVC, XLPE
Insul. Wall Designator: REGULAR



Terminal Part Number: 13595182

Surface Plating: CR

Material Thickness [mm]: 1,40

Cross Section [mm²]: 10,00

*This document is non-contractual
and for information only.*

*For more information, please
consult your local sales office*

Cable Type codes: 2013

Crimp Process: (C) CRIMP ONLY - TERMINAL IS APPLIED CRIMP ONLY

Insulation Range Φ [mm]: 5,50 - 6,00

Seal(s): NONE

Cable type / seal	Arrangement	Nominal Insul. diam [mm]	Tear-out force [N]	CCH [mm]	Tol CCH [mm]	CCW [mm]	Tol CCW [mm]	ICH [mm]	Tol ICH [mm]	ICW [mm]	Tol ICW [mm]
2013 10,00		5,75	1100	5,40	0,05	7,80	0,20	8,50	0,20	8,20	0,20

Cable type code legend:

2013:



Industry Designator: DIN

Conductor Material: COPPER

Conductor Plating: NONE

Insul. Material: PUR, PVC, SYNTHRESIN, XLPE, XLPE/PVDF

Insul. Wall Designator: THIN



Terminal Part Number: 13595182
Surface Plating: CR
Material Thickness [mm]: 1,40
Cross Section [mm²]: 10,00

*This document is non-contractual
and for information only.*

*For more information, please
consult your local sales office*

Cable Type codes: 2028
Crimp Process: (C) CRIMP ONLY - TERMINAL IS APPLIED CRIMP ONLY
Insulation Range Φ[mm]: 5,80 - 6,60
Seal(s): NONE

Cable type / seal	Arrangement	Nominal Insul. diam [mm]	Tear-out force [N]	CCH [mm]	Tol CCH [mm]	CCW [mm]	Tol CCW [mm]	ICH [mm]	Tol ICH [mm]	ICW [mm]	Tol ICW [mm]
2028 10,00		6,20	1100	5,40	0,05	7,80	0,20	8,50	0,20	8,20	0,20

Cable type code legend:

2028: FL RENAULT N1
Industry Designator: DIN
Conductor Material: COPPER
Conductor Plating: NONE
Insul. Material: P/EST, PVC, XLPE
Insul. Wall Designator: REGULAR

