






LOC		DIST		REVISIONS				
F	T	LTR	DESCRIPTION	DATE	DWN	T	APVD	
F			REVISED PER ECR-15-010337	23JUL2015	RK		SC	

1. PINS TO COMPLY WITH AMP SOLDERABILITY SPEC. 108-11-3.
- △ 0.00381 MIN MATTE TIN LEAD OVER 0.00127 MIN NICKEL.
- △ 0.00076 MIN GOLD PLATE IN THE LOCALIZED PLATE AREA, 0.00381 MATTE TIN LEAD IN THE LOCALIZED PLATE AREA, BOTH OVER 0.00127 MIN NICKEL.
- △ 0.00381 MIN MATTE TIN OVER 0.00127 MIN NICKEL.
- △ 0.00076 MIN GOLD PLATE IN THE LOCALIZED PLATE AREA, 0.00381 MATTE TIN IN THE LOCALIZED PLATE AREA, BOTH OVER 0.00127 MIN NICKEL.



RECOMMENDED MOUNTING HOLE PATTERN
FOR 1.57 THICK P.C. BOARD



BRASS, GOLD	△ 5	NYLON, UL94V-0	WHITE	1-794068-1
BRASS, TIN	△ 4	NYLON, UL94V-0	WHITE	1-794068-0
BRASS, GOLD	△ 3	NYLON, UL94V-0	WHITE	794068-2
BRASS, TIN-LEAD	△ 2	NYLON, UL94V-0	WHITE	794068-1
MATERIAL	FINISH	MATERIAL	COLOR	PART NO.

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN S CARPENTER	OBJUN05	TE Connectivity	
DIMENSIONS:		CHK R JONES	29JUL2003	NAME	
mm		APVD R JONES	29JUL2003	PRODUCT SPEC	
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APPLICATION SPEC		SIZE	
0 PLC ± -		WEIGHT		CAGE CODE	
1 PLC ± -		CUSTOMER DRAWING		DRAWING NO	
2 PLC ± 0.13		SCALE 5:1		SHEET 1 OF 1	
3 PLC ± -		REV F		RESTRICTED TO	
4 PLC ± -					
ANGLES ± -					
FINISH					