






Tous droits strictement reserves. Reproduction ou communication a des tiers
interdite sous quelque forme que ce soit sans autorisation écrite du propriétaire.
Propriete de c FCI. Droits de reproduction FCI.


All rights strictly reserved. Reproduction or issue to third parties in any
form whatever is not permitted without written authority from the proprietor.
Property of FCI. Copyright FCI.



SECTION X-X




SECTION Y-Y

mat'l. code NOTE 2 & 5				tolerances unless otherwise specified			CUSTOMER COPY	FCI Electronics www.fciconnect.com		
litr	ecn no	dr	date	linear	.XX ±.01/.X±.3			projection 	title HEADER, QUICKIE SLIMLINE, VERTICAL, 4 WALL HTP	
R	V61660	EPK	11/4/96			.XXX ±.005/.XX±.13				
S	V90594	EPK	3/1/99		XXXX ±.0020/.XXX±.051					
T	V91334	LSS	6/3/99	angles	0° ±2°					
U	V00284	DAI	1/25/00	dr	M.CLOUSER	1/10/90	INCH/MM ↔	product family	HEADER	code
V	V00526	DAI	2/10/00	enrg	M.SMYK	7/10/90		size	dwg no	—
W	V00723	DAI	3/1/00	chr	M.SMYK	10/10/90	scale 1:1	A	88873	sheet 1 of 4
Z	N05-0151	ZC	6/10/05	appd	M.SMYK	10/10/90				
sheet	revision	Z	Z	Z	Z	Z				
index	sheet	1	2	3	4					

KEY FOR PLATING AND OPTIONS				TAIL LENGTH
X	TERMINAL PLATING	RETENTION NOTE 6	ORIENTATION POST NOTE 7	DIM D
-0XX(LF)	15u" / .38u GXT	NO	YES	.120/3.05
-1XX(LF)	15u" / .38u GXT	NO	NO	.120/3.05
-2XX(LF)	30u" / .76u GXT	NO	NO	.445/11.30
-3XX(LF)	15u" / .38u GXT	YES	NO	.120/3.05
-4XX(LF)	30u" / .76u GXT	NO	YES	.120/3.05
-5XX(LF)	30u" / .76u GXT	YES	NO	.120/3.05
-6XX(LF)	30u" / .76u GXT	NO	NO	.120/3.05
-7XX(LF)	30u" / .76u GXT	NO	NO	.105/2.67
-8XX(LF)	30u" / .76u GXT	NO	NO	.085/2.16
-9XX(LF)	15u" / .38u GXT DUPLEX	NO	YES	.105/2.67

NOTES:

- (1) SAME PIN POSITION TOLERANCE APPLIES TO BOTH ENDS OF EACH TERMINAL.
- (2) MOLDING MAT'L: GLASS-FILLED POLYESTER PCT, FLAME RETARDANT
PER UL-94V-0, COLOR: BEIGE
3. 1° MAX DRAFT PERMISSIBLE ON ALL SURFACES.
4. 4 POUNDS/1.8 KILOGRAMS MIN TERMINAL PULL-OUT FORCE.
- (5) TERMINAL MAT'L: PHOSPHOR BRONZE.
- (6) 15 POUNDS / 6.8 KILOGRAMS MAX INSERTION FORCE AND .5 POUNDS/
2.26 KILOGRAMS MIN RETENTION FORCE USING .062/1.57 THICK CIRCUIT
BOARDS AND RECOMMENDED HOLE PATTERN.
- (7) ORIENTATION POSTS ARE UNAVAILABLE WITH RETENTION PINS.
RETENTION PINS ARE UNAVAILABLE WITH ORIENTATION POSTS.
8. P/N'S WITH "T" BEHIND THEM REQUIRE TUBE PACKAGING PER BUS-14-112.
- (9) MAY BE ORDERED WITH G-PAX PACKAGING BY ADDING "G" TO THE
DASH NUMBER PER GES-14-314.
- (10) POSITION #4 POLARIZED ON -206.
- (11) POSITION #20 POLARIZED ON -061.
- (12) POSITION #5 POLARIZED ON -062.
- (13) POSITION #25 POLARIZED ON -363.
- (14) POSITION #3 POLARIZED ON -366
- (15) SOLDER DIP PROCESS ACCEPTABLE (TIN-LEAD TAILS)
- (16) P/N'S WITH "V" BEHIND THEM REQUIRE PICK-UP CAPS.
- (17) "D" DENOTES CUSTOMER SPECIAL.
18. THE HOUSING OF XXXX-XYLF WILL WITHSTAND EXPOSURE TO 260°C
PEAK TEMPERATURE FOR 10 SECONDS IN A WAVE SOLDER PROCESS.
19. 88873-***LF IS JUST A LEAD FREE PRODUCT.



RECOMMENDED HOLE PATTERN
SCALE 3/1

* NOTE 15



2 X 4
STYLE A



2 X 7
STYLE C



2 X 5
STYLE B



2 X 8 THUR 2 X 30
STYLE D

mat'l. code				tolerances unless otherwise specified		CUSTOMER COPY		Electronics www.fciconnect.com		
ltr	ecn no	dr	date	linear	.XX ±.01/.X±.3	projection 	title HEADER, QUICKIE SLIMLINE, VERTICAL, 4 WALL HTP			
Z					.XXX ±.005/.XX±.13					
					XXXX ±.0020/.XXX±.051					
				angles	0° ±2°	INCH/MM scale 1:1	product family		code	
				dr	M.CLOUSER		1/4/93	HEADER		-
				enr	M.SMYK		1/4/93	size		dwg no
				chr	M.SMYK		1/4/93	A		88873
				appd	M.SMYK	1/4/93			sheet	
sheet		revision						2 of		
index		sheet								

Tous droits strictement reserves. Reproduction ou communication a des tiers
Interdite sous quelque forme que ce soit sans autorisation écrite du propriétaire.
Propriete de c FCI. Droits de reproduction FCI.




All rights strictly reserved. Reproduction or issue to third parties in any
form whatever is not permitted without written authority from the proprietor.
Property of FCI. Copyright FCI.

SIZE	TYPE	DIM "Y" REF	NO. OF POS. AT UPPER SIDE	NO. OF POS. AT LOWER SIDE
2 X 2	G	.300/7.64	0	2
2 X 3	G	.100/2.54	0	4
2 X 4	G	.200/5.09	0	4
2 X 5	G	.300/7.64	0	4
2 X 6	G	.200/5.09	0	4
2 X 7	G	.100/2.54	0	6
2 X 8	G	.200/5.09	0	6
2 X 10	F	—	2	7
2 X 12	E	.200/5.09	2	8
2 X 13	E	.300/7.64	3	8
2 X 15	E	.100/2.54	4	10
2 X 17	E	.300/7.64	5	10
2 X 18	F	—	6	11
2 X 20	E	.200/5.09	7	12
2 X 22	F	—	8	13
2 X 25	E	.300/7.64	9	14
2 X 30	F	—	12	17


2X2 THROUGH 2X8

TYPE G




2X10 THROUGH 2X30

TYPE E



TYPE F



mat'l. code				tolerances unless otherwise specified		CUSTOMER COPY		Electronics FCI www.fciconnect.com			
ltr	ecn no	dr	date	linear	.XX ±.01/.X±.13	projection	title	product family			
Z					.XXX ±.005/.XX±.13			INCH/MM	HEADER	code	
					XXXX ±.0020/.XXX±.051					—	
				angles	0° ±2°	scale	size	sheet			
				dr	M.CLOUSER 1/4/93			1:1	A	3 of	
				enr	M.SMYK 1/4/93						
				chr	M.SMYK 1/4/93						
				appd	M.SMYK 1/4/93						
sheet index		revision sheet									

Tous droits strictement reserves. Reproduction ou communication a des tiers
Interdite sous quelque forme que ce soit sans autorisation ecrite du proprietaire.
Propriete de c FCI. Droits de reproduction FCI.



All rights strictly reserved. Reproduction or issue to third parties in any
form whatever is not permitted without written authority from the proprietor.
Property of FCI. Copyright FCI.

PRODUCT NUMBER	DIM A	DIM B	DIM C	STYLE	SIZE
88873-X04 (LF)	.480/12.19	.420/10.67	.100/2.54	A	2 X 2
-X06 (LF)	.580/14.73	.520/13.21	.200/5.08	A	2 X 3
-X06D (LF)	.580/14.73	.520/13.21	.200/5.08	A	2 X 3
-X08 (LF)	.680/17.27	.620/15.75	.300/7.62	A	2 X 4
-X08D (LF)	.680/17.27	.620/15.75	.300/7.62	A	2 X 4
-X09 (LF)	.780/19.81	.720/18.29	.400/10.16	A	2 X 5
-X10 (LF)	.780/19.81	.720/18.29	.400/10.16	B	2 X 5
-X12 (LF)	.880/22.35	.820/20.83	.500/12.70	A	2 X 6
-X14 (LF)	.980/24.90	.920/23.37	.600/15.24	C	2 X 7
-X16 (LF)	1.080/27.90	1.020/25.91	.700/17.78	D	2 X 8
-X20 (LF)	1.280/32.51	1.220/30.99	.900/22.86		2 X 10
-X24 (LF)	1.480/37.59	1.420/36.07	1.100/27.94		2 X 12
-X26 (LF)	1.580/40.13	1.520/38.61	1.200/30.48		2 X 13
-X30 (LF)	1.780/45.21	1.720/43.69	1.400/35.56		2 X 15
-X34 (LF)	1.980/50.29	1.920/48.77	1.600/40.64		2 X 17
-X36 (LF)	2.080/52.83	2.020/51.31	1.700/43.18		2 X 18
-X40 (LF)	2.280/57.91	2.220/56.39	1.900/48.26		2 X 20
-X44 (LF)	2.480/62.99	2.420/61.47	2.100/53.34		2 X 22
-X50 (LF)	2.780/70.61	2.720/69.09	2.400/60.96		2 X 25
-X60 (LF)	3.280/83.31	3.220/81.79	2.900/73.66		2 X 30
-061 (LF)	2.280/57.91	2.220/56.39	1.900/48.26		2 X 20
-062 (LF)	1.980/50.29	1.920/48.77	1.600/40.64	D	2 X 17
-206 (LF)	.580/14.73	.520/13.21	.200/5.08	A	2 X 3
-207 (LF)	.580/14.73	.520/13.21	.200/5.08	A	2 X 3
-363 (LF)	2.780/70.61	2.720/69.09	2.400/60.96	D	2 X 25
-366 (LF)	1.980/50.29	1.920/48.77	1.600/40.64		2 X 17
-934 (LF)	1.980/50.29	1.920/48.77	1.600/40.64		2 X 17
88873-950 (LF)	2.780/70.61	2.720/69.09	2.400/60.96	D	2 X 25

NOTE 17
NOTE 9
NOTE 17
NOTE 9

NOTE 9

NOTE 9

NOTE 11
NOTE 12
NOTE 10

NOTE 13
NOTE 14

mat'l. code				tolerances unless otherwise specified		CUSTOMER COPY	Electronics FCI www.fciconnect.com		
ltr	ecn no	dr	date	linear	.XX ±.01/.X±.3	projection 	title HEADER, QUICKIE SLIMLINE, VERTICAL, 4 WALL HTP		
Z					.XXX ±.005/.XX±.13				
					XXXX ±.0020/.XXX±.051				
				angles	0° ±2°		product family		code
				dr	M.CLOUSER 1/4/93		HEADER		-
				enr	M.SMYK 1/4/93		size		sheet
				chr	M.SMYK 1/4/93		dwg no		4 of
				appd	M.SMYK 1/4/93	scale	A		
sheet index		revision sheet				1:1			

cage code

ACAD

PDM: Rev:X

STATUS Released 26 Printed: Apr 12, 2011