




THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.




DETAIL A




DETAIL B



DETAIL C




DETAIL D




NOTE:
1. DIMENSIONS IN [] ARE
IN MILLIMETERS.

STYLE A



STYLE B



PART NUMBER	SEE DETAIL	"A" +/- .062	"B"	MARKER ACROSS	TUBING COLOR	SEE STYLE	MARKERS PER ROLL
H050X025H1T	A	0.50 [12.70]	.75 [19.1]	4	WHITE	A	2000
H075X025H1T	B	0.75 [19.05]	1.00 [25.4]	2			1000
H100X025H1T	C	1.00 [25.40]	.75 [19.1]	2			1000
H150X025H1T	D	1.50 [38.10]	1.00 [25.4]	1			500
H200X025H1T	E	2.00 [50.80]	.75 [19.1]	1	YELLOW	A	500
H050X025H2T	A	0.50 [12.70]	.75 [19.1]	4			2000
H075X025H2T	B	0.75 [19.05]	1.00 [25.4]	2			1000
H100X025H2T	C	1.00 [25.40]	.75 [19.1]	2			1000
H150X025H2T	D	1.50 [38.10]	1.00 [25.4]	1	BLACK	A	500
H200X025H2T	E	2.00 [50.80]	.75 [19.1]	1			500
H050X025H3T	A	0.50 [12.70]	.75 [19.1]	4			2000
H075X025H3T	B	0.75 [19.05]	1.00 [25.4]	2			1000
H100X025H3T	C	1.00 [25.40]	.75 [19.1]	2	RED	A	1000
H150X025H3T	D	1.50 [38.10]	1.00 [25.4]	1			500
H200X025H3T	E	2.00 [50.80]	.75 [19.1]	1			500
H050X025H4T	A	0.50 [12.70]	.75 [19.1]	4			2000
H075X025H4T	B	0.75 [19.05]	1.00 [25.4]	2	RED	A	1000
H100X025H4T	C	1.00 [25.40]	.75 [19.1]	2			1000
H150X025H4T	D	1.50 [38.10]	1.00 [25.4]	1			500
H200X025H4T	E	2.00 [50.80]	.75 [19.1]	1			500
H050X025H1T-B	A	0.50 [12.70]	.75 [19.1]	4	WHITE	B	10000
H075X025H1T-B	B	0.75 [19.05]	1.00 [25.4]	2			5000
H100X025H1T-B	C	1.00 [25.40]	.75 [19.1]	2			5000
H150X025H1T-B	D	1.50 [38.10]	1.00 [25.4]	1			2500
H200X025H1T-B	E	2.00 [50.80]	.75 [19.1]	1			2500

							TITLE H***X025H*T OPTIMUM COMPUTER PRINTABLE MIL. SPEC. HEAT SHRINK MARKERS CUSTOMER DRAWING					
9	4/28/15	RVU	SEWH	JHAC	ADD NEW COLUMN OF MARKERS PER ROLL.	GAECN02781	ITEM REVISION NAME I00923NG/11			PANDUIT		
8	1/19/15	RVU	SEWH	MSAD	REVISED TO CURRENT PANDUIT LOGO.	GAECN02539	DATASET FILE NAME I00923NG_DC_C10432/11K					
7	4/12/12	RVU			REVISED H150 PARTS TO SHOW ALL MARKERS ARE ONLY 1.5" LONG.	6731	UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: IN [mm] .x ± .12 [3.05] .xxx ± .020 [0.508] .xx ± .062 [1.57] ANGLES ±  THIRD ANGLE PROJECTION			MATERIAL: HEATSHRINK TUBING G1UHS31, 3.5 WIDE LINER		
6	5/21/09	RVU			+/- .12, +/- .062, +/- .020 WAS +/- .03, +/- .032, +/- .010. HT: .25 +/- .032 WAS .250. MAT'L, HSK TUBING G1UHS31, 3.5 WIDE LINER WAS G1UHS. ADD "A" +/- .062. ADD STYLE B VIEW FOR BULK BOX. UPDATE VIEWS.	5593						
REV	DATE	BY	CHK	APR	DESCRIPTION	ECN	DRAWN BY RVU	DATE 8/1/06	CHK MSAD	SCALE NTS	SHT 1 OF 1	SIZE A