








P.C. MOUNTING



SCHEMATIC



Specifications:




Contact rating:	switching: 100mA, 6V; 25mA, 24V non-switching: 100mA, 50V DC
Contact resistance:	100mOhm max.
Insulation resistance:	100MOhm min. at 100V DC
Dielectric strength:	250CV, 50Hz for the duration of 1 minute
Operating temperature:	-20°C to +80°C
Storage temperature:	-55°C to +85°C
Mechanical life:	min. 1 000 cycles
Operating force:	max. 400gf
Soldering conditions:	reflow soldering: max.: 250°C, 10sec.
Mounting:	on pc-board - SMD
Material:	Cover / base: PPS, resin, black Slider: nylon, yellow Contact: copper alloy, gold plated over nickel Terminal: copper alloy, gold flash over nickel Tape: polyimide

Poles	A
4	6.81
6	9.35
8	11.89
10	14.43



Tolerances:			Date	Name	DHS 1xx	
			06/13	dr		
					30 28 77	
					knitter-switch	
					Page	
Modifications	Date	Name			1/2	

Packaging:



xx	A (mm)	B (mm)	(C) (mm)	D (mm)	Packaging unit (pcs. / reel)
04	12.0	24.0	11.5	-	1 000
06	16.0	24.0	11.5	-	700
08	12.0	24.0	11.5	-	1 000
10	16.0	32.0	14.2	28.4	700



Tolerances:			Date	Name	DHS 1xx		
			06/13	dr			
			knitter-switch		30 28 77	Page	
						2/2	
Modifications	Date	Name					