







N=Number of poles



PCB LAYOUT



SIGN	DATE	DESCRIPTION	APPROVER

THIS IS CAD DRAWING, DO NOT REVISE MANUALLY!!!

SPECIFICATIONS

VOLTAGE & CURRENT:	300 V, 20 A
WITHSTANDING VOLTAGE:	AC 2000 V/Min
INSULATION RESISTANCE:	1000 MΩ OR MORE AT DC 500 V
TEMPERATURE RANGE:	-40 °C ~ +105 °C
SCREW TORQUE VALUE:	12 Lb-In.
WIRE RANGE:	22 - 12AWG
1) MOLDED PARTS:	THERMOPLASTIC, UL 94 V-0 BLACK
2) TERMINAL:	BRASS, 0.8t, Tin PLATED
3) TERMINAL SCREWS:	STEEL, Ni PLATED, M3.5

APPROVAL: 
RoHS Compliant

PART NUMBER:

OSTYK504XX030

NO. OF POLES

02: 2 POLES
03: 3 POLES
04: 4 POLES
:
30: 30 POLES

THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF ON-SHORE TECHNOLOGY, INC. AND SHALL NOT BE REPRODUCED, COPIED OR USED IN ANY MANNER WITHOUT THE PRIOR WRITTEN CONSENT OF ON-SHORE TECHNOLOGY, INC.

 ON-SHORE TECHNOLOGY, INC.							
TITLE				OSTYK-504 Without Flange&Cover Series			
PART NO.				OSTYK504XX030		DWG NO.	OSTYK504XX030.DWG
APPROVED	CHECKED	DESIGNED	DRAWN	CUST NO.			
Shi Jun 2007.07.18	Seamus 2007.07.18	LUCY 2007.7.18	LUCY 2007.7.18				
						UNIT: mm	Tolerance
						SCALE: NONE	X. ±0.50
						REV.: B	X.X ±0.30
							X.XX ±0.10
							X° ±1°

SHEET: 01/01