




SIGN	DATE	DESCRIPTION	APPROVER
		THIS IS CAD DRAWING, DO NOT REVISE MANUALLY Y!!!	

Material

- Insulator: Glass Filled Polyester
- Flammability: UL94V-0
- Color: Black
- Contacts: Brass
- Plating termination: 1.2u" Au min, 50u" Ni

Ratings

- Current: 3A
- Voltage: 250V AC(r.m.s.)
- Contact Resistance: <20mΩ
- Insulation Resistance: >1,000MΩ
- Dielectric Withstanding Voltage: 1500V AC for one minute
- Operating Temperature: -40°C ±105°C
- Solderability: 245°C ± 5°C for 3±0.5 seconds

RoHS Compliant

PLATING

- 1= Full Gold Flash/Nickel (STD)
- 5 = 120u" Tin over 50u" Nickel
- 7 = Selective 15u" Gold/Nickel
- 8 = Selective 30u" Gold/Nickel
- NON-STD may require MOQ

PART NUMBER:

302-RXXX

Number of circuits

Dim. D

- 3.10 - leave blank (standard)
- 2.80 - add 2.8 to end of p/n may require MOQ

 ON-SHORE TECHNOLOGY, INC.								
TITLE		302 Series - Dual Row Right Angle Box Header						
PART NO.		302-RXXX			DWG NO.		302-RXXX.DWG	
APPROVED		CHECKED	DESIGNED	DRAWN	4050		Tolerance	
		Marvin 2003.06.16	Marvin 2003.06.16	Marvin 2003.06.16		UNIT: mm/inches		X. ±0.30/.012
						SCALE: NONE		X.X ±0.20/.008
						REV: B		X.XX ±0.10/.004
SHEET: 01/01							X* ±1°	

THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF ON-SHORE TECHNOLOGY, INC. AND SHALL NOT BE REPRODUCED, COPIED OR USED IN ANY MANNER WITHOUT THE PRIOR WRITTEN CONSENT OF ON-SHORE TECHNOLOGY, INC.

Recommended P.C. Board Layout