

4

3



2

1


used for:

D-SUB

POS.	A -0.76	B $+0.25$	C	D -0.3	Part NO.
9	31.19	16.79	25.00 $+0.12$ -0.13	6.12	163A11069X
15	39.52	25.12	33.30 $+0.15$ -0.1	6.12	163A11079X
25	53.42	38.84	47.04 ± 0.13	5.99	163A11089X
37	69.70	55.30	63.50 ± 0.13	5.99	163A11099X



SEE NOTE 4



Directive 2002/95/EC
„RoHS“
Compliant

b) NOTES:


1. METALSHELLS: STEEL; min. 315pin TIN over 40-80pin NICKEL
2. INSULATORS: PBT GF UL 94 V-0, BLACK
3. CONTACTS: COPPER ALLOY
PLATING: 8pin HARD GOLD OVER min. 50pin NICKEL
SOLDER CUP ACCEPTS CABLE AWG 20
4. CONNECTOR IS PART MARKED: PART-NO. CONEC ABC

APPROVAL * FREIGABE * DEBLOCAGE * AUTOR/ZACON * APPROVAL	
CUSTOMER APPROVAL DATE:	
NAME:	TITLE:
COMPANY NAME:	
APPROVAL * FREIGABE * DEBLOCAGE * AUTOR/ZACON * APPROVAL	

THIS DRAWING MAY NOT BE COPIED OR
REPRODUCED IN ANY WAY, AND MAY NOT
BE PASSED ON TO A THIRD PARTY WITHOUT
WRITTEN PERMISSION.
OWNERSHIP AND COPYRIGHT OF CONEC GmbH
DO NOT ALTER CAD DRAWING BY HAND

1 x b	Ä 2535	18.07.2006	Lehmen
a	Origin		
rev.	description	date	name

tolerance



dim. in mm

1998	date	name
drawn	25.08.	Barcinski
appd.	25.08.	Mickenbecker
norm	DIN 41652	
d-old		

CONEC®

scale:

2:1

material:

SEE NOTES

title:

D-SUB MALE
9-37pos. SOLDER CUP

dwg no:

AutoCAD 2006

DIN-A

16K11FVA

4

sh: 1/1

part no:

SEE TABLE

4

3

2

1