

TM-139 Level Adjuster



Characteristic

A simple level adjuster having excellent performances on waterproof and corrosion resistance.


Application

Devices that are used exterior or in high humidity environments, etc.

Parts List

No.	Part Name	Material	Finish
1	Shaft	SUS304	—
2	Nylon Washer	PA	Primary Color
3	Foot	SUS304	—
4	E-Shaped Snap Ring		

Model No.	A	B	C	C1	D	E	F	G	H	Allowable Vertical Compressive Load kN (kgf)	Net Weight (g)	Code No.
TM-139-1	M20×2.5	61	120.5	100	20.5	9.5	1	4	30	9.81 (1000)	372	5621
TM-139-2	M10×1.5	45	67	50	17	9.0	1	3	17	3.92 (400)	80	5622



TM-256 Level Adjuster




Characteristic

Allowable swinging angle for the shaft is made larger comparing with ordinary products to make it usable even on an inclined surface.
A cross-hole head pin is set on the bottom so that installation can be made easily with a screwdriver.

Application

Office automation appliances /
Vending machines / Machine tools, etc.

Model No.	A	B	C	C1	D	E	F	G	Allowable Vertical Compressive Load kN (kgf)	Net Weight (g)	Code No.
TM-256-1	M12 × φ45 1.75		71	50	21	t2.5	14	(7)	3.92 (400)	89	6271
TM-256-2			91	70					3.92 (400)	103	6272
TM-256-3			121	100					3.92 (400)	125	6273
TM-256-4			151	130					3.92 (400)	147	6274
TM-256-5	M16 × φ60 2.0		96	70	26	t2.9	19	(7.5)	5.89 (600)	213	6275
TM-256-6			126	100					5.89 (600)	249	6276
TM-256-7			156	130					5.89 (600)	289	6277
TM-256-8			186	160					5.89 (600)	329	6278
TM-256-9	M20 × φ60 2.5		126	100	24	t2.9	24	(8)	5.89 (600)	338	6279
TM-256-10			156	130					5.89 (600)	398	6280
TM-256-11			186	160					5.89 (600)	459	6281
TM-256-12			206	180					5.89 (600)	500	6282



Parts List

No.	Part Name	Material	Finish	Quantity
1	Adjuster Bolt	SWCH10R	Zn	1
2	Base	SPCC		1
3	Cross Hole Head Set Pin	SWCH45K		1
4	Washer	PC		1