

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

© COPYRIGHT - By -

ALL RIGHTS RESERVED.

LOC	DIST	REVISIONS				
AD	00	P	LTR	DESCRIPTION	DATE	APVD
			-	SEE SHEET 1	-	-

D

D

C

C

B

B

A

A

9	1.650	33	1.830	68	10 8-104068-8
	2.450	49	2.630	100	8-104068-7
	1.950	39	2.130	80	10 8-104068-6
	1.750	35	1.930	72	10 8-104068-5
	1.050	21	1.230	44	10 8-104068-4
	.800	16	.980	34	8-104068-3
	.600	12	.780	26	10 8-104068-2
	.550	11	.730	24	10 8-104068-1
	.350	7	.530	16	10 8-104068-0
	.300	6	.480	14	10 7-104068-9
	.250	5	.430	12	10 7-104068-8
	.150	3	.330	8	7-104068-7
	1.450	29	1.630	60	10 7-104068-6
	1.200	24	1.380	50	10 7-104068-5
	.950	19	1.130	40	10 7-104068-4
	.700	14	.880	30	10 7-104068-3
	.200	4	.380	10	10 7-104068-2
	.450	9	.630	20	10 7-104068-1
7	1.650	33	1.830	68	6-104068-8
	2.450	49	2.630	100	6-104068-7
	1.950	39	2.130	80	6-104068-6
	1.750	35	1.930	72	6-104068-5
	1.050	21	1.230	44	6-104068-4
	.800	16	.980	34	6-104068-3
	.600	12	.780	26	6-104068-2
	.550	11	.730	24	6-104068-1
	.350	7	.530	16	6-104068-0
	.300	6	.480	14	5-104068-9
	.250	5	.430	12	5-104068-8
	.150	3	.330	8	11 5-104068-7
	1.450	29	1.630	60	5-104068-6
	1.200	24	1.380	50	5-104068-5
	.950	19	1.130	40	5-104068-4
	.700	14	.880	30	5-104068-3
	.200	4	.380	10	5-104068-2
	.450	9	.630	20	5-104068-1
FINISH	C	B	A	NO OF POS	PART NUMBER

8	1.650	33	1.830	68	10 3-104068-8
	2.450	49	2.630	100	10 3-104068-7
	1.950	39	2.130	80	10 3-104068-6
	1.750	35	1.930	72	10 3-104068-5
	1.050	21	1.230	44	10 3-104068-4
	.800	16	.980	34	10 3-104068-3
	.600	12	.780	26	10 3-104068-2
	.550	11	.730	24	10 3-104068-1
	.350	7	.530	16	10 3-104068-0
	.300	6	.480	14	10 2-104068-9
	.250	5	.430	12	10 2-104068-8
	.150	3	.330	8	10 2-104068-7
	1.450	29	1.630	60	10 2-104068-6
	1.200	24	1.380	50	10 2-104068-5
	.950	19	1.130	40	10 2-104068-4
	.700	14	.880	30	10 2-104068-3
	.200	4	.380	10	10 2-104068-2
	.450	9	.630	20	10 2-104068-1
1	1.650	33	1.830	68	1-104068-8
	2.450	49	2.630	100	1-104068-7
	1.950	39	2.130	80	1-104068-6
	1.750	35	1.930	72	1-104068-5
	1.050	21	1.230	44	1-104068-4
	.800	16	.980	34	1-104068-3
	.600	12	.780	26	1-104068-2
	.550	11	.730	24	1-104068-1
	.350	7	.530	16	1-104068-0
	.300	6	.480	14	104068-9
	.250	5	.430	12	104068-8
	.150	3	.330	8	11 104068-7
	1.450	29	1.630	60	104068-6
	1.200	24	1.380	50	104068-5
	.950	19	1.130	40	104068-4
	.700	14	.880	30	104068-3
	.200	4	.380	10	104068-2
	.450	9	.630	20	104068-1
FINISH	C	B	A	NO OF POS	PART NUMBER

104068

THIS DRAWING IS A CONTROLLED DOCUMENT.

DWN

D. CLOUSER

10-3-88

CHK

T. ZOLA

10-3-88

APVD

T. ZOLA

10-3-88

DIMENSIONS:

INCHES

0 PLC

1 PLC

2 PLC

3 PLC

4 PLC

ANGLES

± -

± -

± -

± -

± -

± -

MATERIAL

SEE TABLE

PRODUCT SPEC

108-1093

APPLICATION SPEC

114-25031

WEIGHT

-

CUSTOMER DRAWING

SCALE 4:1

DWN

D. CLOUSER

10-3-88

CHK

T. ZOLA

10-3-88

APVD

T. ZOLA

10-3-88

NAME

TE Connectivity

HEADER ASSEMBLY, VERTICAL SHROUDED,
DOUBLE ROW W/SIDE & END LATCHES,
AMPMODU System 50

SIZE

CAGE CODE

DRAWING NO

RESTRICTED TO

A2

00779

C=104068

-

SHEET

2 of 2

REV

P